

- **Digital speed controller for DC or brushless motors up to 250W**
- Configured using a USB cable and graphical interface

Accessories

- **ESCON Studio** software
(Free download from our site)



ESCON-4Q-50/5



ESCON-USB



ESCON-CABLE

DISCOUNTS

Qty	1+	6+	10+
Disc.	List -7%		On request

Technical Specifications		50V/5A	
- Max power	250W	- Fault	Yes
- Supply voltage	10 to 50 Vdc	- Auxiliary Voltage	+5 Vdc 10 mA max
- Max output current	15A	- Hall sensor supply	+5 Vdc 10 mA max
- Nominal Output current	5A	- Encoder supply	+5 vdc 70mA
- Max motor speed	150 000 rpm	- Aux input supply	-10 /+10 Vdc
- Programmable	No	Parameters	
- Control mode	Current, Speed	- Offset	Yes
Inputs:		- Max speed	Yes
- Limit switches	No	- Max output current	5 A
- Analogue	2,12 bit, +/-10V	- Speed ramp	Yes
- Speed limit	Pot. ext/int, PWM 53.6KHZ	- Current point	15 A
- Enable/Disable	Yes	- Gain	Yes
- Electronic brake	Yes	Protection	
- Stop	No	- Reverse polarity	No
- Direction	Yes	- Surge protection	Yes
- Encoder	A,A/B, B/ -1MHz	- Under voltage	Yes
- Tachometer	Yes	- Overvoltage	Yes
- Regulation	Rxl	- Over Current limit	Limited by regulator
- Serial link	No	- Motor short circuit	Yes
- CAN bus	No	- Input short circuit	Yes
Outputs :		- Supply short circuit	Yes
- USB signal	Mini USB	- Thermal	Yes
- Speed	Yes	- Working temp	-30°/ +45°C
- Current	Yes	- Storage	-40°/ +85°C
- Ready	Yes	- Relative humidity	20/80 % non condensing

Part number	Mounting	Format	Weight (g)	Price each 1 to 5
ESCON-4Q-50/5	Screw M4	115X75,5x24	204	379,04 €
ESCON-USB		USB cable for PC link		22,66 €
ESCON-CABLE		Kit of 4 cables for DC motor		49,44 €

Dimensions in mm

Altri prodotti...



AC

Pastrina di riscontro,
12mm



PPOss

Pastrina con anello,
Inox




SVG

Chiusura a leva
regolabile, Corsa da
118mm a 130,5mm



YG0

Ingranaggio dritto
PRESTAZIONE, Acciaio
35NCD6



M1

Ruota per vite senza
fine, Bronzo



PTA100

Piede snodato con
base stampata Ø100,
15000N



PGM86-M5

Maniglia a ponte,
Termoplastica



BPHF

Sfera portante a
incastro con flangia,
Forte



SSG1

Ingranaggio dritto
Inox, Inox 304L



PTA150

Piede snodato con
base stampata Ø150,
40000N



BAGSS

Anello di bloccaggio
inox, Inox



SC2

Giunto rigido in 2
parti, Ganascia di
serraggio

Prodotti correlati



ESCON

Variatore di velocità
5A, 5 A