

- **Digital speed controller for DC or brushless motors up to 250W**
- Configured using a USB cable and graphical interface

Accessories

- **ESCON Studio** software
(Free download from our site)



ESCON-4Q-50/5



ESCON-USB



ESCON-CABLE

DISCOUNTS

Qty	1+	6+	10+
Disc.	List -7%		On request

Technical Specifications		50V/5A	
- Max power	250W	- Fault	Yes
- Supply voltage	10 to 50 Vdc	- Auxiliary Voltage	+5 Vdc 10 mA max
- Max output current	15A	- Hall sensor supply	+5 Vdc 10 mA max
- Nominal Output current	5A	- Encoder supply	+5 vdc 70mA
- Max motor speed	150 000 rpm	- Aux input supply	-10 /+10 Vdc
- Programmable	No	Parameters	
- Control mode	Current, Speed	- Offset	Yes
Inputs:		- Max speed	Yes
- Limit switches	No	- Max output current	5 A
- Analogue	2,12 bit, +/-10V	- Speed ramp	Yes
- Speed limit	Pot. ext/int, PWM 53.6KHZ	- Current point	15 A
- Enable/Disable	Yes	- Gain	Yes
- Electronic brake	Yes	Protection	
- Stop	No	- Reverse polarity	No
- Direction	Yes	- Surge protection	Yes
- Encoder	A,A/B, B/ -1MHz	- Under voltage	Yes
- Tachometer	Yes	- Overvoltage	Yes
- Regulation	Rxl	- Over Current limit	Limited by regulator
- Serial link	No	- Motor short circuit	Yes
- CAN bus	No	- Input short circuit	Yes
Outputs :		- Supply short circuit	Yes
- USB signal	Mini USB	- Thermal	Yes
- Speed	Yes	- Working temp	-30°/ +45°C
- Current	Yes	- Storage	-40°/ +85°C
- Ready	Yes	- Relative humidity	20/80 % non condensing

Part number	Mounting	Format	Weight (g)	Price each 1 to 5
ESCON-4Q-50/5	Screw M4	115X75,5x24	204	379,04 €
ESCON-USB		USB cable for PC link		22,66 €
ESCON-CABLE		Kit of 4 cables for DC motor		49,44 €


Dimensions in mm

Altri prodotti...




CHM30-MOT

Motoriduttore AC asincrono da 0,09 a 0,22kW, 0.09 a 0.22kW



LAT4

Attuatore lineare a motore 4A, 4 ampere



M1

Ruota per vite senza fine, Plastica lavorata (delrin)




LRR-53

Chiavistello con bloccaggio, Lucchetto a molla acciaio



HLC28

Rinvio angolare a dentatura spiroidale, Fino a 182Nm



PSPE22

Conical flexible shaft handle Ø22, Black PVC




CLSCLP

Forcella serie corta, Corta acciaio



FBL6000_K13

Spazzola al metro, Polipropilene nero striato (PP)



G0

Ingranaggio dritto acciaio, Acciaio 20NCD2



UTKswr

Guida lineare Utilitrack®, Profilo guida a V



MAX26

Motoriduttore DC 12V e 24V DC, da 0,075 a 0,6Nm



BPM_LOK

Pressore a molla con intaglio e puntale a sfera, LONG-LOK - Acciaio

Prodotti correlati



ESCON

Variatore di velocità 5A, 5 A