Stainless steel cable terminal

Sta

EVC


Fork version

- ***Cable terminal to be screwed***
- *Material :*
  Stainless steel 316

Accessories

- **CAB** *cable*
  (tome 1 p.418)





DISCOUNTS

Qty	1+	4+	10+	15+
Disc.	List	-10%	-20%	On request

Part number	For cable ØC	A	ØB	C	L	Weight (g)	Price each 1 to 3
EVC2-37/SS	2	4,5	8	7	37	16,5	
EVC3-50/SS	3	5,5	10	8	50	30,0	
EVC4-52/SS	4	6,5	12	8	52	46,0	

Dimensions in mm

Stainless steel cable terminal

Threaded rod version


EVF

- ***Cable terminal to be screwed***
- *Thread ISO pitch right hand*
- *Delivered with a nut*
- *Material :*
  Stainless steel 316

Accessories

- ***CAB** cable*
  (tome 1 p.418)





DISCOUNTS

Qty	1+	4+	10+	15+
Disc.	List	-10%	-20%	On request

Part number	For cable ØC	ØM	ØB	E	L	Weight (g)	Price each 1 to 3
EVF2-50-M4/SS	2	M4	8	20	50	11,0	
EVF3-56-M4/SS	3	M4	10	20	56	19,0	
EVF4-80-M5/SS	4	M5	12	40	80	51,5	

Dimensions in mm

Stainless steel cable terminal

Sta

EVY


Eye version

- ***Cable terminal to be screwed***
- *Material :*
  Stainless steel 316

Accessories

- **CAB** *cable*
  (tome 1 p.418)





DISCOUNTS

Qty	1+	4+	10+	15+
Disc.	List	-10%	-20%	On request

Part number	For cable ØC	ØA	ØB	L	Weight (g)	Price each 1 to 3
EVY2-37/SS	2	4,5	8	37	13	
EVY3-50/SS	3	5,5	10	50	27	
EVY4-52/SS	4	6,5	12	52	41	

Dimensions in mm

Stainless steel cable terminal


Threaded hole version


EVT

- ***Cable terminal to be screwed***
- *Thread ISO pitch right hand*
- *Delivered with a nut*
- *Material :*
  Stainless steel 316

Accessories

- **CAB** *cable*
  (tome 1 p.418)





DISCOUNTS

Qty	1+	4+	10+	15+
Disc.	List	-10%	-20%	On request

Part number	For cable ØC	ØM	ØB	P	L	Weight (g)	Price each 1 to 3
EVT2-55-M5/SS	2	M5	8	20	55	16,0	
EVT3-65-M5/SS	3	M5	10	25	65	33,0	
EVT4-70-M6/SS	4	M6	12	25	70	51,5	

Dimensions in mm

Altri prodotti...



BOXdhx

Box kit di spine filettate DIN7979D, Box kit - estraibile DIN 7979D



BKGS

Giunto senza gioco Gerwah®, da 1.2 a 450Nm



CNA-CNG

Staffa di montaggio per molla a gas, Staffa di montaggio a squadra p...



CHMBR

Braccio di reazione, Braccio di reazione per riduttori CHM e CHMR



PT880

Pignone di trazione, Serie 880



MHPGR

Manovella ad impugnatura girevole,



BOX-CSss

Fascette di serraggio, Valigetta di fascette inox



SBF

Open flange bearing unit for food industry, cover



LC

Limitatore di coppia ad attrito, 190 a 1800 Nm



SVG

Chiusura a leva regolabile, Corsa da 118mm a 130,5mm



GARQT

Perno di bloccaggio tipo ¼ di giro, ¼ di giro



BOX-TOR-INCH

Valigetta di guarnizioni toriche in nitrile, For fasteners and fitting

Prodotti correlati



ERC

Terminale rapido per cavi, A forcella




ERC

Terminale rapido per cavi, A occhio



ERF

Terminale rapido per cavi, Terminale filettato



CAB

Cavo di fissaggio, Acciaio galvanizzato