Sealing brush strips

FBL

Advantages and applications

Advantages



- No wastage, only the length required is removed from the roll.
- Reduced storage/transport space, each box contains 25 metres.



- Special scissors allow the strip to be cut to the required length.




- Flexible in terms of positioning and fitting.


Applications



- Splash guard for wheel arches on a lorry



- Waterproofness of floor cleaning machines




- Guiding PET bottles

Brush strip horsehair fibres Ø0.2

For ensuring a seal up to 125°C

FBL6000
FBL6001

Brush strip to cut to desired length.



Horsehair fibres

Uses


- *Sealing*
- *Cable entries*
- *Guiding parts*

Materials


- ***Fibres:*** *Horsehair. No risk of static charge, excellent for dusting, brushing, sealing and for applying liquids (can be used as paintbrush)*
  Maximum temperature: +150°C
- ***Support:*** *Thermoplastic rubber.*
  Good UV and ozone resistance. Practically unaffected by most chemicals.
  Working temperature: -40 to +125°C

Info.

- ***Sold in 5 metre lengths.***
- *Maximum length of a single brush is 25 metres.*
- *Special scissors for cutting to length* **FBL-TOOL**



FBL6001
90° profile



FBL6000
Straight profile

DISCOUNTS

Qty	1+	2+	5+
Disc.	List	-10%	On request

Part number Straight profile	90° profile	Bristle diameter (mm)	BH	Length	Stock* Straight profile	Stock* 90° profile	Price each Straight profile	90° profile
Black horsehair								
FBL6000-K19	-	0,2	15	5m	✔	-	63,64 €	-
FBL6000-K20	-	0,2	20	5m	✔	-	68,86 €	-
FBL6000-K21	FBL6001-K21	0,2	25	5m	-	✔	74,33 €	74,33 €
FBL6000-K23	FBL6001-K23	0,2	40	5m	✔	-	92,79 €	92,79 €
FBL6000-K24	FBL6001-K24	0,2	50	5m	✔	✔	108,10 €	108,10 €
Tools								
FBL-TOOL		Cutting scissors						193,51 €

**Depending on availability - Dimensions in mm*

Tel. +33(0)4 37 496 496 **cial2@hpceurope.com**

Brush strip PA6 fibres Ø0.2 to Ø0.3

Stock*

FBL6000
FBL6001

For ensuring an internal seal

Brush strip to cut to desired length.



PA6 fibres

Uses


- Sealing
- Cable entries
- Guiding parts

Materials

- ***Fibres:*** Polyamide PA6. Standard material for brushes used for cleaning, transporting, guiding or sealing moving pieces.
  Working temperature: -20 to 100°C
- ***Support:*** Thermoplastic rubber.
  Good UV and ozone resistance.
  Practically unaffected by most chemicals.
  Working temperature: -40 to +125°C

Info.

- ***Sold in 5 metre lengths.***
- *Maximum length of a single brush is 25 metres.*
- *Special scissors for cutting to length*
  FBL-TOOL



FBL6001
90° profile

FBL6000
Straight profile

DISCOUNTS

Qty	1+	2+	5+
Disc.	List	-10%	On request

Part number Straight profile	Part number 90° profile	Bristle diameter (mm)	BH	Length	Stock* Straight profile	Stock* 90° profile	Price each Straight profile	Price each 90° profile
Black Polyamide 6 (PA6) fibres								
FBL6000-K1	FBL6001-K1	0,2	10	5m	✔	✔	48,53 €	48,53 €
FBL6000-K2	FBL6001-K2	0,2	15	5m	✔	✔	49,78 €	49,78 €
FBL6000-K3	FBL6001-K3	0,2	20	5m	✔	✔	51,26 €	51,26 €
FBL6000-K4	-	0,2	25	5m	✔	-	52,74 €	-
FBL6000-K5	FBL6001-K5	0,2	30	5m	✔	✔	54,21 €	54,21 €
FBL6000-K7	-	0,3	15	5m	✔	-	49,78 €	-
FBL6000-K8	-	0,3	20	5m	✔	-	51,26 €	-
FBL6000-K9	-	0,3	25	5m	✔	-	52,74 €	-
FBL6000-K10	-	0,3	30	5m	✔	-	54,21 €	-
FBL6000-K11	-	0,3	40	5m	✔	-	57,33 €	-
FBL6000-K12	-	0,3	50	5m	✔	-	60,29 €	-
Tools								
FBL-TOOL	Cutting scissors							193,51 €


**Depending on availability - Dimensions in mm*

Stock Brush strip PA6 fibres Ø0.3 to Ø0.5

For ensuring an internal seal

FBL4004
FBL4005

Brush strip to cut to desired length.



PA6 fibres

Uses


- *Sealing*
- *Cable entries*
- *Guiding parts*

Materials


- ***Fibres:*** *Polyamide PA6. Standard material for brushes used for cleaning, transporting, guiding or sealing moving pieces.*
  Working temperature: -20 to 100°C
- ***Support:*** *Thermoplastic rubber. Good UV and ozone resistance. Practically unaffected by most chemicals.*
  Working temperature: -40 to +125°C

Info.

- ***Sold in 5 metre lengths.***
- *Maximum length of a single brush is 25 metres.*
- *Special scissors for cutting to length* **FBL-TOOL**



FBL4005
90° profile



FBL4004
Straight profile

DISCOUNTS

Qty	1+	2+	5+
Disc.	List	-10%	On request

Part number Straight profile	90° profile	Bristle diameter (mm)	BH	Length	Stock* Straight profile	Stock* 90° profile	Price each Straight profile	90° profile
Black Polyamide 6 (PA6) fibres								
FBL4004-K8	-	0,3	20	5m	✔	-	140,75 €	-
FBL4004-K9	-	0,3	30	5m	✔	-	147,61 €	-
FBL4004-K13	-	0,5	30	5m	✔	-	147,61 €	-
FBL4004-K14	-	0,5	40	5m	✔	-	154,69 €	-
FBL4004-K15	-	0,5	50	5m	✔	-	161,80 €	-
FBL4004-K18	FBL4005-K15	0,5	80	5m	✔	✔	193,81 €	193,81 €
Tools								
FBL-TOOL	Cutting scissors							193,51 €

**Depending on availability - Dimensions in mm*

Tel. +33(0)4 37 496 496 **cial2@hpceurope.com**


Brush strip PP fibres Ø0.2

Stock*

FBL6000
FBL6001

For ensuring an external seal

Brush strip to cut to desired length.



Uses


- Sealing
- Cable entries
- Guiding parts

Materials

- **Fibres:** Polypropylene. No water absorption, good resistance to chemicals...
  Working temperature: -20 (occasional) to 80°C
- **Support:** Thermoplastic rubber.
  Good UV and ozone resistance. Practically unaffected by most chemicals.
  Working temperature: -40 to +125°C

Info.

- **Sold in 5 metre lengths.**
- Maximum length of a single brush is 25 metres.
- Special scissors for cutting to length
  FBL-TOOL



DISCOUNTS

Qty	1+	2+	5+
Disc.	List	-10%	On request

Part number Straight profile	Part number 90° profile	Bristle diameter (mm)	BH	Length	Stock* Straight profile	Stock* 90° profile	Price each Straight profile	Price each 90° profile
Black horsehair								
FBL6000-K13	FBL6001-K13	0,2	10	5m	✔	✔	44,56 €	44,56 €
FBL6000-K14	FBL6001-K14	0,2	15	5m	✔	✔	44,98 €	44,98 €
FBL6000-K15	FBL6001-K15	0,2	20	5m	✔	✔	45,38 €	45,38 €
FBL6000-K17	FBL6001-K17	0,2	30	5m	✔	-	46,66 €	46,66 €
FBL6000-K18	FBL6001-K18	0,2	40	5m	✔	✔	47,69 €	47,69 €
Tools								
FBL-TOOL		Cutting scissors						193,51 €

*Depending on availability - Dimensions in mm

Brush strip PP fibres Ø0.3

For ensuring an external seal

FBL4004
FBL4005

Brush strip to cut to desired length.



PP fibres

Uses


- *Sealing*
- *Cable entries*
- *Guiding parts*

Materials


- ***Fibres:*** *Polypropylene. No water absorption, good resistance to chemicals...*
  Working temperature: -20 (occasional) to 80°C
- ***Support:*** *Thermoplastic rubber.*
  Good UV and ozone resistance. Practically unaffected by most chemicals.
  Working temperature: -40 to +125°C

Info.

- ***Sold in 5 metre lengths.***
- *Maximum length of a single brush is 25 metres.*
- *Special scissors for cutting to length*
  FBL-TOOL



FBL4005
90° profile



FBL4004
Straight profile

DISCOUNTS

Qty	1+	2+	5+
Disc.	List	-10%	On request

Part number Straight profile	90° profile	Bristle diameter (mm)	BH	Length	Stock* Straight profile	Stock* 90° profile	Price each Straight profile	90° profile
Black Polyamide 6 (PA6) fibres								
FBL4004-K34	-	0,3	30	5m	✔	-	130,13 €	-
FBL4004-K35	-	0,3	40	5m	✔	-	132,49 €	-
FBL4004-K36	FBL4005-K31	0,3	50	5m	✔	✔	134,99 €	134,99 €
FBL4004-K37	FBL4005-K32	0,3	60	5m	✔	-	137,47 €	137,47 €
FBL4004-K38	-	0,3	70	5m	✔	-	151,08 €	-
Tools								
FBL-TOOL				Cutting scissors				193,51 €

**Depending on availability - Dimensions in mm*

Tel. +33(0)4 37 496 496 **cial2@hpceurope.com**

WEB 04/2021

HPC

Our other products


T5M_T10M

T type timing belt per metre, T5 Steel cored polyurethane


GE1006

Elastic ringed latch, Hooks into a slot


PCS50SS

Chain sprocket - Stainless steel, 12.7mm (DIN 08B-1)


EHD12

Internal epicyclic servo reducers, from 60 to 140 Nm


UTKpwrr

V shaped channel UtiliTrak®, V rail


CHMR75

Worm and wheel gear reducer, up to 298 Nm


BPTR

End cap for round tube, Standard


RPP8

RPP heavy duty timing belt, RPP8


PDR-RD

Mounting feet with integrated castors,


PW_PWG2

Worm - precision range, Steel


ESCON

Speed controller 5A accessories, Kit of 4


PM4

Worm and wheel set, Hardened steel

Complementary products


STRIP

Sealing brush strip, 3m length


STRIPF

Sealing brush strip, 1m length

Altri prodotti...



Motoriduttore DC 12V e 24V DC, da 0,07 a 0,2Nm



Ingranaggio dritto in plastica stampata , Nylon stampato



Cinghia di posizionamento T, T5 Poliuretano armatura in acciaio



Cerniera a molla, to install



Guida lineare Utilitrack®, Carello a rotelle - rivestimento polimero



Pistoncino a molla - Supporto, fissaggio perpendicolare alla serratura



Ruota per profili alluminio, Girevole con freno



Ingranaggio dritto di precisione, Inox 303




Giunto a soffietto Gerwah®, da 22 a 600Nm



Chiusura ¼ di giro per bloccaggio , Manopola plastica o inox



Motoriduttore DC 12V e 24V DC, da 4 a 9 Nm



Elementi di giunzione, Angolare semicircolare

Prodotti correlati



Spazzola strip, Lunghezza 3m



Spazzola strip, Lunghezza 1m