Latch clamp with lock


Lockable


GAC


- ***Snap closing***
- *Supplied with 2 identical keys*
- *Latch clamp and strike plates supplied separately*
- *Material:*
  Galvanised steel
  Stainless steel 304


Advantage

- *Can be locked using a key*

















Hole layout

DISCOUNTS

Qty	1+	10+	20+	50+	100+
Disc	List	-3%	-5%	-10%	On request

Part number	Material	Finish	A	B	C	D	E	Weight (g)	Stock*	Price each 1 to 9
Latch clamp										
GAC-106	steel	Galvanized	106,5	40,0	17,0	-	-	132	✔	17,59 €
GAC-106/SS	S/steel 304	Natural	106,5	40,0	17,0	-	-	132	✔	28,25 €
Strike plate										
GAC-106G	steel	Galvanized	-	-	-	28	25	24	✔	3,74 €
GAC-106G/SS	S/steel 304	Natural	-	-	-	28	25	24	✔	7,11 €

Dimensions in mm

Altri prodotti...



Vite di giunzione metallo/legno, Acciaio



Perno serie corta inox, Inox - serie corta



Riduttore a ruota e vite senza fine, fino a 298 Nm



Base per tirante chiusura in gomma, Base



Manopola, zigrinata



Vite senza fine , Acciaio temprato



Ingranaggio dritto acciaio , Acciaio 20NCD2



Dado di sicurezza, Per bloccaggio assiale



Perno autobloccante, Regolabile



Ruota di rinvio, Serie 882



Ruota fissa con piastra, Acciaio -



Ingranaggio conico - Acciaio C43 - ECO, 3:1

Prodotti correlati



Chiusura a leva con serratura, Riscontro grezzo



Chiusura a leva, Standard



Chiusura a leva, Standard



Chiusura a leva regolabile, Corsa da 82mm a 92mm