
Cylindrical ballscrew nut

GBMz


For KGS ballscrew


- **Nut for ballscrew**
- Multiple starts
- Axial backlash: 0.2mm
- Material:
  16 MnCr5 or 100Cr6



Accessory

- See **KGS** ballscrew (the pitch and the diameter must be identical to those of the nut)







DISCOUNTS

Qty	1+	2+	6+	11+
Disc.	List	-7%	-13%	On request

Part number	ØD1g6	ØD2	L1	L2	L3	L4	L5	BxT
GBM-Z-2020-RH	35	1,5	30	14	11,50	12	9	5x3
GBM-Z-2050-RH	35	1,5	56	40	14	20	18	5x2
GBM-Z-3220-RH	53	1,5	55	35	16	20	17,5	6x4
GBM-Z-3240-RH	53	1,5	50	30	16	25	12,5	6x4
GBM-Z-5020-RH	85	1,5	73,50	50	16,75	30	22	6x2,5

Part number	For ballscrew Ø	Movement per rev (mm)	Load dynamic C (kN)	Load static Co (kN)	Weight (kg)	Price each
GBM-Z-2020-RH	20	20	9,00	19,10	0,15	439,05 €
GBM-Z-2050-RH	20	50	7,90	19,00	0,30	479,95 €
GBM-Z-3220-RH	32	20	19,50	65,00	0,50	587,04 €
GBM-Z-3240-RH	32	40	11,50	33,50	0,45	590,09 €
GBM-Z-5020-RH	50	20	61,70	178,40	1,40	1 044,60 €

Dimensions in mm

Altri prodotti...


CHINV

Cerniera invisibile, Invisibile - Apertura fino a 90°


SSG2_304L

Ingranaggio dritto Inox, Inox 304L


PW_PWG05

Vite senza fine di precisione, Acciaio


DPAR_DKON

Piedino antivibrante parabolico, Acciaio


ACLLPP

Sistema di chiusura, Chiusura a molla


H1

Ingranaggio elicoidale ad assi incrociati a 90°, Plastica lavorata ...


EZY


Piedino antivibrante cilindrico, Acciaio


PSG25

Ingranaggio dritto di precisione, Acciaio 35NCD6 pretrattato


PCLA_M

Maniglia a ripresa - femmina, Plastica


RAGb

Cylindrical brush track, For gentle


ZY

Piedino antivibrante cilindrico, Inox


PCLA_T

Maniglia a ripresa - maschio, Plastica

Prodotti correlati


KGS

Vite a ricircolo di sfere al metro, Vite a sfere rullata, al metro