

Curved track for plate chain






GCB880T For chain ranges 880 TAB and 881 TAB

- Used to support and guide CAP880T and CAP881T/SS plate chains
- Material
High density Black DESLIDUR

Info.

- Comprises 2 tracks (carry and return)



DISCOUNTS

Qty.	1+	5+	10+
Disc.	List	-5%	On request

Part number	For chain	AG (mm)	R1 (mm)	K (mm)	Weight (kg)	Price each 1 to 4
GCB880T-82	CAP880T-82 CAP881T-82/SS	100	500	82,5	2,4	132,22 €
GCB880T-114	CAP880T-114 CAP881T-114/SS	130	610	114,3	4,4	256,76 €

Dimensions in mm

Altri prodotti...



CHA35
Cerniera ad avvitare,
Cerniera



BAC110
Contenitore a becco,
Aggancio orientabile



VDSQ
Bloccaggio scorrevole
per la regolazione,
Bloccaggio rapido per
prof...



CLB_M
Maniglia a ripresa,
Zamak



BPTR
Tappo per tubo tondo,
Standard



SH1
Ingranaggio elicoidale
ad assi paralleli,
Plastica lavorata
(delrin)



VML
Volantino a lobi, Vite
di pressione



ZG4
Ingranaggio dritto in
plastica, Plastica
lavorata (delrin)




VTLM
Volantino a 3 lobi,
Poliammide - Acciaio



CF
Perno folle, Standard -
acciaio



D19 D29
Molla di compressione
al metro acciaio, al
metro



BCM_MPBT
Spazzola cilindrica
modulare, Filo
poliestere PBT

Prodotti correlati



CAP880
Catena a tapparella,
Stretta serie 880



CAP881
Catena a tapparella,
Stretta serie 881



SDG
Supporto con tirante
ad occhio, Plastica