
Curved track for plate chain


GCB880T For chain ranges 880 TAB and 881 TAB

- ***Used to support and guide CAP880T and CAP881T/SS plate chains***
- *Material*
  High density Black DESLIDUR

Info.

- *Comprises 2 tracks (carry and return)*





DISCOUNTS

Qty.	1+	5+	10+
Disc.	List	-5%	On request

Part number	For chain	AG (mm)	R1 (mm)	K (mm)	Weight (kg)	Price each 1 to 4
GCB880T-82	CAP880T-82 CAP881T-82/SS	100	500	82,5	2,4	132,22 €
GCB880T-114	CAP880T-114 CAP881T-114/SS	130	610	114,3	4,4	256,76 €

Dimensions in mm

Altri prodotti...



EX

Albero per riduttori E, Albero semplice per riduttori E



DOMI80

Kit di raccordo, Kit di raccordo XZ



ERC

Terminale rapido per cavi, A forcella



SH1

Ingranaggio elicoidale ad assi paralleli, Acciaio 20NCD2



PWC

Inserti filettati, Kit Powercoil - con o senza attrezzo di posa



UFX

Giunto elastico UNEFLEX, range



ZG2

Ingranaggio dritto in plastica, Plastica lavorata (delrin)



RFK38C

Riduttore ipoide inox, fino a 200 Nm



PTA150

Piede snodato con base stampata Ø150, 40000N



CQA30

Slitta di regolazione miniatura, 30



SHW

Rondella semplice , Acciaio



BABFCFO

Perno autobloccante, Boccole di fissaggio con flangia cilindrica

Prodotti correlati



CAP880

Catena a tapparella, Stretta serie 880



CAP881

Catena a tapparella, Stretta serie 881



SDG

Supporto con tirante ad occhio, Plastica