
- ***Brushes for the cleaning and removal of dust***
- *Materials:*
  Twisted galvanised steel
  Natural silk covering




Application

- *Cleaning of hollow containers (tubes, bottles, holes)*
- *Cleaning of hard-to-reach areas*

Advantage

- *Anti-static*





Cleaning of hard-to-reach areas

DISCOUNTS

Qty	1+	10+	25+	50+
Disc.	List	-5%	-10%	On request

Part number	Brush diameter ØD	Brush length L1	Total length L2	Stock*	Price each 1 to 9
GPL15-100/SO	15	80	300	✔	7,00 €
GPL20-100/SO	20	80	300	-	8,27 €
GPL25-100/SO	25	80	300	✔	7,38 €

Dimensions in mm

Altri prodotti...



HK

Accessorio di serraggio manuale, Serraggio manuale LWH



LVT

Mini martinetto motorizzato 4A, 4 ampere



BZY_SS

Antivibrante elastico cilindrico inox, Inox



RT61ss

Calettatore di bloccaggio, Coppia media/bassa



FBL6000_K1

Spazzola al metro fibre PA6 da Ø0,2 a Ø0,3, Poliammide nero 6 - pi...



MEB

Ingranaggio conico in plastica stampata, 1:1



CLM

Attacco per forcella, Corta acciaio



BABM

Perno autobloccante con segmenti filettati, Acciaio



ACLCHARJ

Cerniera ad avvitare, Adjusts in 2 directions



Q4

Cuscinetto a doppia corona di sfere, Radiale - Acciaio



PTAF100-PAMF100

Piede fissabile con base lamiera Ø100, Ø 100



GP75


Chiusura a leva molla a trazione compensata, Standard (GP75)

Prodotti correlati



GPLss

Scovolo, inox



GPLac

Scovolo, acciaio



GPLbr

Scovolo, ottone



GPLny

Scovolo, nylon