Deburring and stripping stainless steel


GPLSS


- ***Stainless steel deburring brushes***
- *Materials:*
  Twisted galvanised steel
  Stainless steel covering



Applications

- *Deburring of pin holes, rivet holes, tapped holes, intersecting holes*
- *Cleaning of hollow containers (tubes, bottles, holes)*
- *Cleaning of hard-to-reach areas*
- *Removing rust*
- *Cleaning*
- *Stripping*





Deburring a gear bore

DISCOUNTS

Qty	1+	10+	25+	50+
Disc.	List	-5%	-10%	On request

Part number	Brush diameter ØD	Brush length L1	Overall length L2	Stock*	Price each 1 to 9
GPL5-100/SS	5	100	300	✔	10,03 €
GPL8-100/SS	8	100	300	✔	8,58 €
GPL10-100/SS	10	100	300	✔	7,84 €
GPL12-100/SS	12	100	300	✔	7,84 €
GPL15-100/SS	15	100	300	✔	7,94 €
GPL20-100/SS	20	100	300	✔	8,22 €
GPL25-100/SS	25	100	300	✔	8,29 €

Dimensions in mm

Altri prodotti...


PSG25S

Ingranaggio dritto di precisione, Inox 316


NSA

Connettore rinvio d'angolo, Articolato


RCC_RCX

Rondella sferica - DIN6319, concava


UCFL_PBT

Supporto a flangia ovale con cuscinetto, Polimero e inox


PTAF100-PAMF100

Piede fissabile con base lamiera Ø100, Ø 100


BUH77

Motoriduttore DC 12V e 24V DC, da 0.1 a 2 Nm


GP75

Chiusura a leva molla a trazione compensata, Standard (GP75)


RTE

Rotex®, elastico, acciaio


KH

Manicotto a sfere, Leggera


CHAEpac

Square decorative screwed hinges, carbon fibre reinforced



PW_PWG05

Ruota di precisione, Bronzo


FUSS

Ghiera autofrenante per cuscinetto, Ghiera autofrenante - rondella i...

Prodotti correlati


GPLac

Scovolo, acciaio


GPLbr

Scovolo, ottone


GPLny

Scovolo, nylon


GPLso

Scovolo, seta