# HTD type tooth bar stock

## Steel


## HTD8M-BAR




- ***Bar stock to be cut to length by the customer***
- *The overall length is the same as the maximum length*
- *Material : Steel C40*

**Info.**

- *We are unable to modify this product*



-30%**




**DISCOUNTS**

| Qty. | 1+ | 6+ | 20+ | 40+ |
|---|---|---|---|---|
| Disc. | List | -12% | -25% | On request |

| Part number | Z Teeth | ØD External | Length of teeth LD | Total length LT | Price each 1 to 5 |
|---|---|---|---|---|---|
| 18HTD8M-BAR | 18 | 44,47 | 200 | 200 | 40,51 € |
| 19HTD8M-BAR | 19 | 47,01 | 200 | 200 | 43,29 € |
| 20HTD8M-BAR | 20 | 49,56 | 200 | 200 | 45,65 € |
| 21HTD8M-BAR | 21 | 52,11 | 200 | 200 | 47,51 € |
| 22HTD8M-BAR | 22 | 54,65 | 200 | 200 | 49,83 € |
| 23HTD8M-BAR | 23 | 57,20 | 200 | 200 | 52,15 € |
| 24HTD8M-BAR | 24 | 59,75 | 200 | 200 | 54,47 € |
| 25HTD8M-BAR | 25 | 62,29 | 200 | 200 | 55,86 € |
| 26HTD8M-BAR | 26 | 64,84 | 200 | 200 | 60,54 € |
| 28HTD8M-BAR | 28 | 69,93 | 200 | 200 | 66,61 € |
| 30HTD8M-BAR | 30 | 75,03 | 200 | 200 | 75,89 € |
| 32HTD8M-BAR | 32 | 80,12 | 200 | 200 | 88,10 € |
| 34HTD8M-BAR | 34 | 85,21 | 200 | 200 | 95,92 € |
| 35HTD8M-BAR | 35 | 87,76 | 200 | 200 | 106,27 € |
| 36HTD8M-BAR | 36 | 90,30 | 200 | 200 | 111,45 € |
| 38HTD8M-BAR | 38 | 95,40 | 200 | 200 | 124,45 € |
| 40HTD8M-BAR | 40 | 100,49 | 200 | 200 | 136,33 € |
| 44HTD8M-BAR | 44 | 110,67 | 200 | 200 | 161,75 € |
| 48HTD8M-BAR | 48 | 120,86 | 200 | 200 | 189,24 € |

*Dimensions in mm*

# Altri prodotti...



PRF-SRA

Sistema di chiusura per profili alluminio, Serruta



RJA10_03

Guarnizione in gomma, Da agganciare



DOMI80

Slitta di regolazione Domino 80, Slitta DOMILINE 80 con contatore e ...



ATZY

Antivibrante elastico sgolato, Acciaio



CHA35

Cerniera ad avvitare, Hinge



PAMF120

Articulated fixable foot, pressed bolt-down base Ø 120, Ø 120



T25-BAR

Barra dentata, T2.5




CFC

Pressore a molla con esagono incassato, A contatto elettrico



PO

Maniglia a ponte - Multi-settore, Foro cieco maschiato



NSKB

Guida mini Drylin® N, Rail end cap



H3

Ingranaggio elicoidale ad assi incrociati a 90°, Acciaio 20NCD2



RT61ss

Calettatore di bloccaggio, Coppia media/bassa

## Prodotti correlati



HTD5M-BAR

Barra dentata per cinghia RPP, HTD5