Conical elasto buffer for foodstuff sector

E-KONBLU — Female mounting

- ***Rubber buffer suitable for use in the food industry***
- *FDA compliant*
- *Materials :*
  Frame: 316 stainless steel
  Cylinder: FDA-compliant blue silicon
- *Medium hardness, Shore 55A*
- *Temperature range : -30 °C to +180 °C*

stainless steel


NEW !

For foodstuff industry



Applications

- *End stop*
- *Supporting foot*



DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	10%	-20%	On request

Part number	ØG	ØD	H	T	Stiffness (N/mm)	Load (N)	Price each 1 to 5
E-KON6-25-17/SS/BLU	M6	25	17	6	102	571	
E-KON8-30-15/SS/BLU	M8	30	15	8	185	1036	
E-KON10-50-17/SS/BLU	M10	50	17	10	677	3554	


Dimensions in mm

Conical elasto buffer for foodstuff sector

Male mounting


D-KONBLU

- ***Rubber buffer suitable for use in the food industry***
- *FDA compliant*
- *Materials:*
  Frame: 316 stainless steel
  Cylinder: FDA-compliant blue silicon
- *Medium hardness, Swhore 55A*
- *Temperature range: -30 °C to +180 °C*



Applications

- *End stop*
- *Supporting foot*



DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	10%	-20%	On request

Part number	ØG	ØD	H	L	Stiffness (N/mm)	Load (N)	Price each 1 to 5
D-KON6-25-17/SS/BLU	M6	25	17	18	80	448	
D-KON8-30-15/SS/BLU	M8	30	15	20	265	1530	
D-KON10-50-17/SS/BLU	M10	50	17	28	640	3584	

Dimensions in mm

Altri prodotti...



Pattino Drylin® W, Pattino




Piede snodato con base stampata Ø40, 3000N



Molla a gas inox, Inox



Piede snodato tutto inox Ø80, Ø 80



Supporto antivibrante cabina conico, Piastra a base ovale



Maniglia a ripresa Hygienic Usit®, Inox



Copiglia a scatto, A scatto



Supporto per estremità dell'albero, A soletta



Box kit di spine filettate DIN7979D,



Anello di sollevamento,



Profilato alluminio standard, 45 x 45 mm



Cuscinetto radiale a sfere, Inox

Prodotti correlati



Piedino antivibrante parabolico, Acciaio



Piedino antivibrante parabolico, inox



Piedino antivibrante conico silicone, Fissaggio maschio



Piedino antivibrante parabolico, Acciaio