Spring return latch


LRR


Steel or stainless steel


- ***Spring loaded single bolt***
- *Rolled knot hinge*
- *Material:*
  White galvanized steel
  Stainless steel 304

Advantages


- *Simple locking*
- *Retractable pivot*







Right handed



Left handed

DISCOUNTS

Qty	1+	50+	100+
Disc.	Net	-10%	On request


Part N°	Version	Stock*	Price each 1 to 49
Steel version			
LRR-53-26/D	Right	-	2,82 €
LRR-53-26/G	Left	-	2,82 €
Stainless steel version			
LRR-53-26/G/SS	Left	-	5,64 €
LRR-53-26/D/SS	Right	-	5,64 €

All dimensions in mm

Altri prodotti...


LRR


Chiavistello con perno prismatico, Lucchetto a molla


GBMz

Dado per vite a sfere, Dado cilindrico a circuiti multipli


SHNbr

Dado esagonale - DIN934, Ottone


EPRF

Dado flangiato per madrevite a passo lungo, Dado flangiato -fino a 4...


M

Manicotto per giunto cardanico, Accessori


NK17

Guida mini Drylin® N, Larghezza 17 mm


SEH

Attrezzo di bloccaggio a tirante, A tirante - inox


NTMbr

Grano punta in ottone, punta in ottone


PSG15

Ingranaggio dritto di precisione, Acciaio


UGH40

Unità di guida tipo H, Per martinetti Ø 40


CAP881

Catena a tapparella, Stretta serie 881


HG8-ECO

Ingranaggio dritto acciaio, Acciaio C45

Prodotti correlati


LRR-53

Chiavistello con bloccaggio, Lucchetto a molla acciaio


LRRss

Interblocco di sicurezza, Chiusura a molla - inox


LRR

Chiavistello con perno prismatico, Lucchetto a molla


LRR22

Small dimension latch with locking system, Aluminium