Carabiner DIN5299 steel

DIN

MAC

Metal diameter 5 to 12mm

- ***Type C Carabiner***
- *White zinc plated steel*
- *Product carries no certification marking*




Application

- *The breaking strength is obtained by multiplying the SWL by a factor of safety of 4*

Info

- *Not suitable for climbing*
- *Also exists in stainless steel*



DISCOUNTS

Qty	1+	20+	40+	60+	80+	100+
Disc.	List	-5%	-10%	-15%	-20%	On request

Part number	ØD	L	A	C	SWL (kg)	Weight (g)	Price each 1 to 19
MAC5-50	5	50	8	7	50	16	1,37 €
MAC6-60	6	60	8	8	90	26	1,56 €
MAC7-70	7	70	11	9	150	44	2,11 €
MAC8-80	8	80	12	10	190	62	2,14 €
MAC9-90	9	90	13	11	230	92	2,35 €
MAC10-100	10	100	16	13	310	126	2,84 €
MAC11-120	11	120	19	17	340	192	3,54 €
MAC12-140	12	140	20	19	380	256	4,80 €

Altri prodotti...



LRH

Vite trapezoidale a doppia inclinazione, a doppia inclinazione - 1 f...



PRF-SRA

Sistema di chiusura per profili alluminio, Serruta



VELM6

Supporto avvitabile per rotolo a strappo fermacavi, Poliammide



ASH

Anello di sollevamento, dritto a saldare



SVR5

Martinetto a vite - Vite rotante, Con madrevite esterna



BPM_LOK

Pressore a molla con intaglio e puntale a sfera, LONG-LOK - Inox 303



MRS

Cremagliera sezione metrica, Inox



BG

Giunto Oldham, con vite a pressione



RT25

Calettatore di bloccaggio, Coppia media/elevata



BABpss

Perno autobloccante, Inox



PTRSS

Pignone tendicatena, Per ambienti aggressivi



LSAG

Albero scanalato a sfere, Carello - da 514 N a 15386 N

Prodotti correlati



MACss

Moschettone inox, Inox