


- ***Digital motor servo amplifier for driving motors* (>90W)**
- *Accepts limit switch inputs*
- *Small size*
- *Easily configured using a PC, RS232 cable required (not supplied)*





Accessories

- ***MDPOT-10T/10K*** *Control potentiometer*
- *Power supplies*



Technical specifications	30V/3A		
- Max Power	90W	- Under voltage	Yes
- Power Supply	10 to 30 Vdc	- Over-current	Adjustable
- Max permanent output current	3A	- Motor short circuit	Yes
- Operating mode	PWM, 1 quadrant	- Short circuit on inputs	Yes
Inputs		**Environment**	
- Speed control	External voltage 0/10V	- Working temperature	0 to 40°C
- Enable	Voltage free contact (earthed)	- Storage temperature	-40 to +85°C
- Direction	Voltage free contact (earthed)	- Relative humidity	20 t0 80 %non-condensing
- Limit switches	2 Voltage free contacts (earthed)	**Connections**	
Outputs		- Connectors	Spring loaded terminals, pitch 2.54mm.
- Ready	Open collector, 30Vdc 20mA		Wire size : 0.14 to 1.5mm2
Controls		- Connectors (motor + supply)	Screw clamp terminals, pitch 3.81mm .
- Max speed	Analogue voltage		Wire size : 0.14 to 1.5mm2
- Max current	Analogue voltage	**Mechanical characteristics**	
Protection		- Dimensions	50x100x32mm
- Reverse polarity	Resettable fuse	- Weight	105g
- Over voltage	Yes	- Mounting:	Uses M4 screws

DISCOUNTS

Qty.	1+	6+	10+
Disc.	List.	-7%	on request

Part number	Mounting	Screw spacing cable	Weight (g)	Price each 1 to 5
NANODC-1Q-30/3	M4 screw	34x54	0,11	125,25 €
NANODC-RS232	Cable NANO DC - RS232			94,29 €

Dimensions in mm

Altri prodotti...



Carrello Drylin® W, Carrello



Ruota per vite senza fine, Bronzo



Giunto elastico Uneflex®, economica



Boccola di posizionamento, Acciaio



Kit di raccordo, Kit di raccordo XZ



Cuscinetto radiale a sfere, Acciaio



Piastrina di riscontro piatta per chiusura, 22mm



Coppia ruota e vite senza fine , Acciaio non temprato



Riduttore a ruota e vite senza fine, fino a



Accessori di collegamento, Kit di



Elementi di giunzione, Giunto di



Volantino a 3 lobi, Poliammide - Ottone

Prodotti correlati



Motoriduttore DC 12V e 24V DC, da 4 a 9 Nm



Motoriduttore DC 12V e 24V DC, da 1.5 a 6 Nm