
Angular connector

Universal

NDS

- ***Offers multiple connection possibilities for vacuum gripping system elements***
- *Material :*
  Aluminium
- *Fixing kit not supplied*




Advantages

- *Compatible with 20-30mm profiles and 40-60mm profiles with rectangular mounting holes*


Accessories

- *PRF-ECLM8 nut*
- *M8 screw, length 20-22mm*

NEW !







Typical mounting arrangement


DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØA	B	C	ØD	Weight (g)	Price each 1 to 9
NDS-1/4/C	G1/4"	30	29-39	G1/4"	94	30,28 €

Dimensions in mm

Altri prodotti...


GPLac


Scovolo, acciaio


CHMR30

Riduttore a ruota e vite senza fine, fino a 28 Nm


PSG25S

Ingranaggio dritto di precisione, Inox 316


PCF2

Supporto antivibrante cabina conico, Piastra a base ovale


DER71

Motore inox AC asincrono da 0,25 a 0,37kW, 0.25 a 0.37kW


SLBS

Pistoncino a molla, Tutto inox


DOMI50

Accessori di collegamento, Piastra


SDG


Supporto con tirante ad occhio, Plastica


CLB_T

Maniglia a ripresa - maschio, Zamak


CAP821

Catena a tapparella dritta, Larga serie 821


PM4

Ruota per vite senza fine, Plastica lavorata


TB8

Cuscinetto assiale a rulli cilindrici, Acciaio

Prodotti correlati


PRF_ECL_

Fissaggio, Dado quadrato con linguetta - Acciaio