Digital position indicator

Size XS New


OP2


3 digit display

- ***3 digit display (red digit displays tenths), displays up to 999***
- *Shaft driven position indicator*
- *3 digit display to display and control a linear movement (or an angle) that is driven by a rotating control shaft.*
- *Non-flammable shock-proof technopolymer housing*
- *Ingress protection: IP64*
- *Max temperature: 80 °C*
- *Height of digits: 6 mm with magnifying lens*
- *Bore for shaft 30H7, other diameters will require reducing sleeve*
- *Offset of anti rotation pin: 18 mm*
- *Internal and external metal parts are stainless steel*



Miniature





Mounting

- Insert the indicator over the shaft ensuring that the anti-rotation pin is inserted into the 6 mm hole drilled previously. Set the display to its initial reading (zero) and tighten the locking screw

Bore diameter

- Bores of 8, 10 and 12 mm are available.
- For an 8 or 10 mm bore, replace 12R in the Par N° with 8R or 10R



Display



View A



SX DX



View B

DISCOUNTS

Qty	1+	5+	10+	15+	25+
Disc.	List	-6%	-12%	-20%	On request

Part number	View	Pitch (mm)	Display after 1 revolution (mm)	Max speed (rpm)	Counting direction	Price each 1 to 4
OP2-A10-DX-12R	A	1	01 0	800	clockwise	92,70 €
OP2-A20-DX-12R	A	2	02 0	350	clockwise	92,70 €
OP2-A30-DX-12R	A	3	03 0	250	clockwise	92,70 €
OP2-A40-DX-12R	A	4	04 0	200	clockwise	92,70 €
OP2-A50-DX-12R	A	5	05 0	150	clockwise	92,70 €
OP2-B10-DX-12R	B	1	01 0	800	clockwise	92,70 €
OP2-B20-DX-12R	B	2	02 0	350	clockwise	92,70 €
OP2-B30-DX-12R	B	3	03 0	250	clockwise	92,70 €
OP2-B40-DX-12R	B	4	04 0	200	clockwise	92,70 €
OP2-B50-DX-12R	B	5	05 0	150	clockwise	92,70 €
OP2-A10-SX-12R	A	1	01 0	800	anti-clockwise	92,70 €
OP2-A20-SX-12R	A	2	02 0	350	anti-clockwise	92,70 €
OP2-A30-SX-12R	A	3	03 0	250	anti-clockwise	92,70 €
OP2-A40-SX-12R	A	4	04 0	200	anti-clockwise	92,70 €
OP2-A50-SX-12R	A	5	05 0	150	anti-clockwise	92,70 €
OP2-B10-SX-12R	B	1	01 0	800	anti-clockwise	92,70 €
OP2-B20-SX-12R	B	2	02 0	350	anti-clockwise	92,70 €
OP2-B30-SX-12R	B	3	03 0	250	anti-clockwise	92,70 €
OP2-B40-SX-12R	B	4	04 0	200	anti-clockwise	92,70 €
OP2-B50-SX-12R	B	5	05 0	150	anti-clockwise	92,70 €

Dimensions in mm

Altri prodotti...



BLM

Pressore liscio a molla, Corpo inox



PCLA_M

Maniglia a ripresa - femmina, Plastica



DOMI_MD

Tavola rotante di regolazione Domino, 40/1



BABS

Perno autobloccante a sfere inox 630, Inox temprato



G4

Ingranaggio dritto acciaio , Acciaio 20NCD2




CHB

Riduttore a ruota e vite senza fine, fino a 41 Nm



VML

Volantino a lobi, Vite di pressione



GMK17_P

Guida prodotto laterale piatta, Per imbottigliamento e imballaggio



MSP19

Inserto con piastrina a incollare



PRES5HR

Pressa manuale da banco, Pressione fino



E50

Riduttore a rinvio angolare, da 3 a 41



LAT1

Attuatore lineare a motore, 1 ampere

Prodotti correlati



EP7

Indicatore di posizione elettronico, 5 cifre



LFM

Vite trapezoidale acciaio, Acciaio semiduro - 1 filetto



SHA_PTR

Volantino pieno, Poliammide