Articulated foot with sheet metal base Ø80

Max load: 10,000N
Rubber sole in EPDM, blue

PAMF80


- ***Articulated adjustable levelling feet***
- *Axial articulation +/- 10°*
- *With non-slip sole in EPDM Blue*
- *Stainless steel in shiny finish*
- *Materials:*
  Base: shiny 304 stainless steel sheet
  Thread: 304 stainless steel, supplied without nut
  Sole: EPDM blue


Options

- *Other thread dimensions on request*
- *316 grade Stainless steel on request*

Advantages

- *Hygienic special sole for easy cleaning.*
- *Food processing, Pharmaceutical and Chemical Environment*





DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc.	Price	-5%	-10%	-15%	On request

Part N°	ØD	ØF	B	A	A/F	G	H	Static load(N)	Price per unit 1 to 5
PAMF80-12-100/EB	80	M12	100	35	14	25	135	10000	36,75 €
PAMF80-12-150/EB	80	M12	150	35	14	25	185	10000	38,83 €
PAMF80-16-75/EB	80	M16	75	35	13	25	110	10000	37,24 €
PAMF80-16-125/EB	80	M16	125	35	13	25	160	10000	39,90 €
PAMF80-16-175/EB	80	M16	175	35	13	25	210	10000	42,53 €
PAMF80-20-100/EB	80	M20	100	38	17	25	138	10000	42,53 €
PAMF80-20-150/EB	80	M20	150	38	17	25	188	10000	45,16 €
PAMF80-20-200/EB	80	M20	200	38	17	25	238	10000	49,11 €

**Within the limits of available stock - Dimensions in mm*

Our other products



KS

Key, Stainless steel - Keystock



PRF_GAL

Roller for aluminium profile, Fixing kit for roller concentric



PRF-SMA

Closing system, Easily adjustable lock



CHTRP

Single and dual output gearboxes, Up to 87,3Nm



ACLRP

Wheel, Integrated bearing



HAS

Captive C washer, Slotted flat headed shoulder screw



SLBW

Indexing plunger, Weldable - Steel



SDB

Locating bolt support bracket, Mounting holes at 90° to locating bolt



ESCB

Support base, Bipod support element with cross support



LC

Friction torque limiter, 190 to 1800 Nm



RFK48B

Hypoid gearbox - Stainless steel, up to 350 Nm



DB

Bevel gear - Steel 60C40, 2:1

Complementary products



PTA50ssEB

Articulated foot with sheet metal base, Articulated foot



PTA80ssEB

Articulated foot with sheet metal base, Articulated foot



PTA100ssEB

Articulated foot with sheet metal base, Articulated foot



PAMF100EB

Articulated foot with sheet metal base, Articulated foot

Altri prodotti...



YG1

Ingranaggio dritto PRESTAZIONE, Acciaio 35NCD6



MRA_SS

Maglia rapida, Inox



BOXdhx

Box kit di spine filettate DIN7979D, Box kit - estraibile DIN 7979D



MBEX

Riduttore manuale, Manovella estremità esagonale



CHAR7520

Cerniera a molla, avvitabile



GG1

Ingranaggio dritto rettificato, Acciaio trattato



BAC105

Contenitore a becco, 8mm




COA-COG

Staffa di montaggio per molla a gas, Staffa di montaggio piana per s...



BABss

Perno autobloccante inox 303, Inox 303



LAT1

Attuatore lineare a motore 1A, 1 ampere



RTTss

Calettatore di bloccaggio, Coppia



CHAC4040NP

Cerniera, Quadrata con rivetto senza fori

Prodotti correlati



PTA50ssEB

Piede snodato con base stampata Ø50, 4000N



PTA80ssEB

Piede snodato con base stampata Ø80, 10000N



PTA100ssEB

Piede snodato con base stampata Ø100, 15000N



PAMF100EB

Piede snodato con base stampata fissabile Ø100, Piede snodato