

## C45 steel

## Pitch 1/4"


**Economy range**



- Pitch 1/4" (6,35mm)
- Roller diameter 3,3mm
- Material:  
C45 UNI7845 steel
- **HPC are unable to modify these parts**
- \*\*The prebore dimensions are given as a guide only and are subject to change

### Accessories

- Chain part number **SUA-250/M**



### DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

Part number	Z teeth	ØP	ØD	ØM	ØA**	E	Weight (kg)	Price each
PCS25-8	8	16,58	19,4	10	6	12	0,01	2,01 €
PCS25-9	9	18,56	21,4	11,5	6	12	0,01	2,14 €
PCS25-10	10	20,55	23,3	13	6	12	0,02	2,18 €
PCS25-11	11	22,54	25,3	15	8	13	0,02	2,22 €
PCS25-12	12	24,53	27,3	17	8	13	0,02	2,22 €
PCS25-13	13	26,53	29,3	17	8	13	0,03	2,60 €
PCS25-14	14	28,53	31,3	17	8	13	0,03	2,72 €
PCS25-15	15	30,53	33,3	20	8	13	0,04	3,06 €
PCS25-16	16	32,55	35,3	22	8	14	0,05	3,40 €
PCS25-17	17	34,55	37,3	22	8	14	0,05	4,07 €
PCS25-18	18	36,56	39,4	25	8	14	0,06	4,45 €
PCS25-19	19	38,58	41,4	25	8	14	0,06	4,79 €
PCS25-20	20	40,58	43,4	25	8	14	0,06	4,92 €
PCS25-21	21	42,60	45,4	30	8	14	0,08	5,30 €
PCS25-25	25	50,66	53,5	30	8	14	0,10	6,98 €
PCS25-28	28	56,71	59,5	30	8	16	0,12	8,50 €
PCS25-29	29	58,73	61,5	30	8	16	0,12	9,00 €
PCS25-30	30	60,75	63,6	30	8	16	0,13	9,13 €
PCS25-32	32	64,78	67,6	30	8	16	0,13	10,56 €
PCS25-33	33	66,80	69,6	30	8	16	0,14	11,06 €
PCS25-34	34	68,82	71,6	30	8	16	0,17	11,19 €
PCS25-35	35	70,84	73,6	30	8	16	0,17	11,70 €
PCS25-36	36	72,85	75,6	30	8	16	0,15	12,20 €
PCS25-37	37	74,87	77,7	30	8	16	0,18	14,30 €
PCS25-38	38	76,89	79,7	30	8	16	0,16	15,78 €
PCS25-39	39	78,91	81,7	30	8	16	0,19	17,22 €
PCS25-40	40	80,93	83,7	30	8	16	0,17	18,77 €

Dimensions in mm

**0 825 88 6000**  
Service 0,15 € / min  
+ prix appel

## Altri prodotti...




CCL  
Capocorda ad  
occhiello, Acciaio



PMC48\_M8  
Supporto antivibrante  
a campana, Piastra a  
base ovale



PRF\_SDD\_1820  
Supporto per sensore  
Ø18 e Ø20, ø18 e ø20



CYS  
Anello di arresto  
interno DIN472,  
interno DIN 472



BEAS  
Star shaped anti-  
static handle, Star,  
anti-static



CHA38\_SS  
Cerniera su facciata  
ad avvitare inox, Su  
facciata



GCT  
Copiglia per tubo, Clip  
per tubo




F7-SN  
Visualizzatore  
multifunzione,  
Supporto snodato



EBC  
Dado cieco Hygienic  
Design®, Compatto



SHNbr  
Dado esagonale -  
DIN934, Ottone



B  
Ingranaggio conico -  
Acciaio 60C40, 1:1



GE  
Chiusura a leva,  
Miniature

## Prodotti correlati



SUA4  
Catena semplice al  
metro, Acciaio



SUA4\_L  
Giunzione per catena  
al metro, Maglia di  
giunzione - acciaio