
Chain sprocket with hardened teeth

DIN08B-1
1/2”

C45 tempered steel



- **Pitch 12,7mm (DIN 08B-1)**
- Roller diameter 8,51mm
- Materials:
  C45 steel UNI7845
  Hardened teeth 45-53HRC





Accessory


- **SBR-500/M** chain

Info

- DIN 6885 keyway on the central tooth line
- Threaded hole on key and at 90°







DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

Part N°	Z Teeth	ØP	ØD	ØM	E	ØA	K (H9)	T2	ØT	Price each 1 to 5
PCS50-12H-12K						12	4	1,80	M4	8,17 €
PCS50-12H-14K						14	5	2,30	M4	8,17 €
PCS50-12H-15K						15	5	2,30	M4	8,17 €
PCS50-12H-16K	12	49,07	53,90	33	28	16	5	2,30	M4	8,17 €
PCS50-12H-18K						18	6	2,80	M5	8,17 €
PCS50-12H-19K						19	6	2,80	M5	8,17 €
PCS50-12H-20K						20	6	2,80	M5	8,17 €
PCS50-13H-12K						12	4	1,80	M4	8,70 €
PCS50-13H-14K						14	5	2,30	M4	8,70 €
PCS50-13H-15K						15	5	2,30	M4	8,70 €
PCS50-13H-16K						16	5	2,30	M4	8,70 €
PCS50-13H-18K	13	53,06	57,90	37	28	18	6	2,80	M5	8,70 €
PCS50-13H-19K						19	6	2,80	M5	8,70 €
PCS50-13H-20K						20	6	2,80	M5	8,70 €
PCS50-13H-22K						22	6	2,80	M5	8,70 €
PCS50-13H-24K						24	8	3,30	M6	8,70 €

All dimensions in mm

Part N°	Z Teeth	ØP	ØD	ØM	E	ØA	K (H9)	T2	ØT	Price each 1 to 5
PCS50-14H-14K						14	5	2,30	M4	9,40 €
PCS50-14H-15K						15	5	2,30	M4	9,40 €
PCS50-14H-16K						16	5	2,30	M4	9,40 €
PCS50-14H-18K						18	6	2,80	M5	9,40 €
PCS50-14H-19K	14	57,07	61,60	41	28	19	6	2,80	M5	9,40 €
PCS50-14H-20K						20	6	2,80	M5	9,40 €
PCS50-14H-22K						22	6	2,80	M5	9,40 €
PCS50-14H-24K						24	8	3,30	M6	9,40 €
PCS50-14H-25K						25	8	3,30	M6	9,40 €
PCS50-15H-14K						14	5	2,30	M4	10,34 €
PCS50-15H-15K						15	5	2,30	M4	10,34 €
PCS50-15H-16K						16	5	2,30	M4	10,34 €
PCS50-15H-18K						18	6	2,80	M4	10,34 €
PCS50-15H-19K						19	6	2,80	M5	10,34 €
PCS50-15H-20K	15	61,09	65,90	45	28	20	6	2,80	M5	10,34 €
PCS50-15H-22K						22	6	2,80	M5	10,34 €
PCS50-15H-24K						24	8	3,30	M6	10,34 €
PCS50-15H-25K						25	8	3,30	M6	10,34 €
PCS50-15H-28K						28	8	3,30	M6	10,34 €
PCS50-15H-30K						30	8	3,30	M6	10,34 €
PCS50-16H-15K						15	5	2,30	M4	11,11 €
PCS50-16H-16K						16	5	2,30	M4	11,11 €
PCS50-16H-18K						18	6	2,80	M4	11,11 €
PCS50-16H-19K						19	6	2,80	M5	11,11 €
PCS50-16H-20K	16	65,10	69,50	50	28	20	6	2,80	M5	11,11 €
PCS50-16H-22K						22	6	2,80	M5	11,11 €
PCS50-16H-24K						24	8	3,30	M6	11,11 €
PCS50-16H-25K						25	8	3,30	M6	11,11 €
PCS50-16H-28K						28	8	3,30	M6	11,11 €
PCS50-16H-30K						30	8	3,30	M6	11,11 €
PCS50-17H-15K						15	5	2,30	M4	11,65 €
PCS50-17H-16K						16	5	2,30	M4	11,65 €
PCS50-17H-18K						18	6	2,80	M4	11,65 €
PCS50-17H-19K						19	6	2,80	M5	11,65 €
PCS50-17H-20K	17	69,11	74,00	52	28	20	6	2,80	M5	11,65 €
PCS50-17H-22K						22	6	2,80	M5	11,65 €
PCS50-17H-24K						24	8	3,30	M6	11,65 €
PCS50-17H-25K						25	8	3,30	M6	11,65 €
PCS50-17H-28K						28	8	3,30	M6	11,65 €
PCS50-17H-30K						30	8	3,30	M6	11,65 €
PCS50-18H-16K						16	5	2,30	M4	12,26 €
PCS50-18H-18K						18	6	2,80	M4	12,26 €
PCS50-18H-19K						19	6	2,80	M5	12,26 €
PCS50-18H-20K						20	6	2,80	M5	12,26 €
PCS50-18H-22K						22	6	2,80	M5	12,26 €
PCS50-18H-24K	18	73,14	77,80	56	28	24	8	3,30	M6	12,26 €
PCS50-18H-25K						25	8	3,30	M6	12,26 €
PCS50-18H-28K						28	8	3,30	M6	12,26 €
PCS50-18H-30K						30	8	3,30	M6	12,26 €
PCS50-18H-32K						32	10	3,30	M8	12,26 €
PCS50-18H-35K						35	10	3,30	M8	12,26 €


Chain sprocket with hardened teeth Ste DIN

DIN08B-1 1/2”

C45 tempered steel



- **Pitch 12,7mm (DIN 08B-1)**
- Roller diameter 8,51mm
- Materials:
  C45 steel UNI7845
  Hardened teeth 45-53HRC




Accessory

- **SBR-500/M** chain

Info

- DIN 6885 keyway on the central tooth line
- Threaded hole on key and at 90°



DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

Part N°	Z Teeth	ØP	ØD	ØM	E	ØA	K (H9)	T2	ØT	Price each 1 to 5
PCS50-19H-19K						19	6	2,80	M5	14,55 €
PCS50-19H-20K						20	6	2,80	M5	14,55 €
PCS50-19H-22K						22	8	3,30	M6	14,55 €
PCS50-19H-24K						24	8	3,30	M6	14,55 €
PCS50-19H-25K	19	77,16	82,00	60	28	28	8	3,30	M6	14,55 €
PCS50-19H-28K						28	8	3,30	M6	14,55 €
PCS50-19H-30K						30	10	3,30	M8	14,55 €
PCS50-19H-32K						32	10	3,30	M8	14,55 €
PCS50-19H-35K						35	10	3,30	M8	14,55 €
PCS50-20H-19K						19	6	2,80	M5	15,20 €
PCS50-20H-20K						20	6	2,80	M5	15,20 €
PCS50-20H-22K						22	6	2,80	M5	15,20 €
PCS50-20H-24K						24	8	3,30	M6	15,20 €
PCS50-20H-25K	20	81,19	85,80	64	28	25	8	3,30	M6	15,20 €
PCS50-20H-28K						28	8	3,30	M6	15,20 €
PCS50-20H-30K						30	8	3,30	M6	15,20 €
PCS50-20H-32K						32	10	3,30	M8	15,20 €
PCS50-20H-35K						35	10	3,30	M8	15,20 €

All dimensions in mm

Part N°	Z Teeth	ØP	ØD	ØM	E	ØA	K (H9)	T2	ØT	Price each 1 to 5
PCS50-21H-19K						19	6	2,80	M5	15,90 €
PCS50-21H-20K						20	6	2,80	M5	15,90 €
PCS50-21H-22K						22	6	2,80	M5	15,90 €
PCS50-21H-24K						24	8	3,30	M6	15,90 €
PCS50-21H-25K	21	85,22	90,10	68	28	25	8	3,30	M6	15,90 €
PCS50-21H-28K						28	8	3,30	M6	15,90 €
PCS50-21H-30K						30	8	3,30	M6	15,90 €
PCS50-21H-32K						32	10	3,30	M8	15,90 €
PCS50-21H-35K						35	10	3,30	M8	15,90 €
PCS50-23H-20K						20	6	2,80	M5	17,00 €
PCS50-23H-22K						22	6	2,80	M5	17,00 €
PCS50-23H-24K						24	8	3,30	M6	17,00 €
PCS50-23H-25K						25	8	3,30	M6	17,00 €
PCS50-23H-28K	23	93,27	98,10	70	28	28	8	3,30	M6	17,00 €
PCS50-23H-30K						30	8	3,30	M6	17,00 €
PCS50-23H-32K						32	10	3,30	M8	17,00 €
PCS50-23H-35K						35	10	3,30	M8	17,00 €
PCS50-23H-38K						38	10	3,30	M8	17,00 €
PCS50-24H-20K						20	6	2,80	M5	18,19 €
PCS50-24H-22K						22	6	2,80	M5	18,19 €
PCS50-24H-24K						24	8	3,30	M6	18,19 €
PCS50-24H-25K						25	8	3,30	M6	18,19 €
PCS50-24H-28K	24	97,29	102,70	70	28	28	8	3,30	M6	18,19 €
PCS50-24H-30K						30	8	3,30	M6	18,19 €
PCS50-24H-32K						32	10	3,30	M8	18,19 €
PCS50-24H-35K						35	10	3,30	M8	18,19 €
PCS50-24H-38K						38	10	3,30	M8	18,19 €
PCS50-25H-20K						20	6	2,80	M5	18,80 €
PCS50-25H-22K						22	6	2,80	M5	18,80 €
PCS50-25H-24K						24	8	3,30	M6	18,80 €
PCS50-25H-25K						25	8	3,30	M6	18,80 €
PCS50-25H-28K	25	101,33	105,80	70	28	28	8	3,30	M6	18,80 €
PCS50-25H-30K						30	8	3,30	M6	18,80 €
PCS50-25H-32K						32	10	3,30	M8	18,80 €
PCS50-25H-35K						35	10	3,30	M8	18,80 €
PCS50-25H-38K						38	10	3,30	M8	18,80 €
PCS50-27H-22K						22	6	2,80	M5	22,19 €
PCS50-27H-25K						25	8	3,30	M6	22,19 €
PCS50-27H-28K						28	8	3,30	M6	22,19 €
PCS50-27H-30K	27	109,40	114,00	70	30	30	8	3,30	M6	22,19 €
PCS50-27H-32K						32	10	3,30	M8	22,19 €
PCS50-27H-35K						35	10	3,30	M8	22,19 €
PCS50-27H-38K						38	10	3,30	M8	22,19 €
PCS50-30H-25K						25	8	3,30	M6	25,63 €
PCS50-30H-28K						28	8	3,30	M6	25,63 €
PCS50-30H-30K						30	8	3,30	M6	25,63 €
PCS50-30H-32K	30	121,50	126,00	80	30	32	10	3,30	M8	25,63 €
PCS50-30H-35K						35	10	3,30	M8	25,63 €
PCS50-30H-38K						38	10	3,30	M8	25,63 €

Altri prodotti...


PM2

Vite senza fine, Acciaio non temprato


CHM110

Riduttore a ruota e vite senza fine, fino a 980 Nm


PRF-SCREEN-5

Screen support, Support with 5 axes of rotation


PRF_PF

Elementi di ancoraggio, Staffa di fissaggio


PR821

Ruota di rinvio, Serie 821 e 805


BPFL

Supporto a flangia ovale con cuscinetto, Lamiera


PCS62SS

Pignone a catena - Inox, 15.875mm (DIN 08B-1)


BWU

Guida lineare di precisione, da 1510 N a 10500 N


RCC_RCX

Rondella sferica - DIN6319, convessa


CRM

Cremagliera in nylon stampato, Nylon


PRES3HR

Pressa manuale da banco, Pressione fino


SERB

Serratura a camme, Serratura a camme

Prodotti correlati


SUA4

Catena semplice al metro, Acciaio


SUA4_L

Giunzione per catena al metro, Maglia di giunzione - acciaio


PCS50

Pignone a catena - acciaio, 12.7mm (DIN08B-1)


PCS_PA6

, 12.7mm (DIN 08B-1)