Detectable plastic palm grip

New

PDM Thermoplastic identifiable by metal detectors

- ***Operating element for sensitive sectors***
- *In the event of breakage during production in sensitive sectors such as the food industry, the plastic fragments are easily identified by metal detectors, enabling them to be disposed of quickly*
- *Material :*
  Detectable thermoplastic (glass-fibre reinforced polyamide), EU10/2011 and FDA compliant (colour RAL7021)
  Components in polished 316L stainless steel
- *Operating temperature: -20°C to +100°C*





Application

- *Food industry*
- *Pharmaceutical industry*
- *Packaging industry*


Info.

- *Metal detectable plastic*
- *Detection volume ≥ 0.027 cm³*
- *Food-grade materials*





Typical application



DISCOUNTS

Qty	1+	6+	10+	25+
Disc.	List	-5%	-10%	On request

Part Number	ØD	ØD1	ØD2	H	H2	H3	T	Price each 1 to 5
PDM25-5	M5	25	10,0	18	9	7,0	9	10,88 €
PDM32-6	M6	32	13,5	22	12	9,5	12	13,24 €
PDM40-6	M6	40	13,5	26	14	10,0	12	16,51 €
PDM40-8	M8	40	13,5	26	14	10,0	12	16,51 €
PDM50-8	M8	50	19,0	32	18	12,0	17	22,45 €
PDM50-10	M10	50	19,0	32	18	12,0	17	22,45 €

Dimensions in mm

New


Detectable plastic palm grip

Thermoplastic identifiable by metal detectors PDM

- ***Operating element for sensitive sectors***
- *In the event of breakage during production in sensitive sectors such as the food industry, the plastic fragments are easily identified by metal detectors, enabling them to be disposed of quickly*
- *Material :*
  Detectable thermoplastic (glass-fibre reinforced polyamide), EU10/2011 and FDA compliant (colour RAL7021)
  Components in polished 316L stainless steel
- *Operating temperature: -20°C to +100°C*

NEW !






Application


- *Food industry*
- *Pharmaceutical industry*
- *Packaging industry*

Info.

- *Metal detectable plastic*
- *Detection volume*
  ≥ 0.027 cm³
- *Food-grade materials*



Typical application



DISCOUNTS

Qty	1+	6+	10+	25+
Disc.	List	-5%	-10%	On request

Part Number	ØD	ØD1	ØD2	H	H2	H3	L	Price each 1 to 5
PDM25-5-10	M5	25	10	18	9	7	10	11,24 €
PDM25-5-15	M5	25	10	18	9	7	15	11,24 €
PDM25-5-20	M5	25	10	18	9	7	20	11,24 €
PDM32-6-10	M6	32	13,5	22	12	9,5	10	12,27 €
PDM32-6-15	M6	32	13,5	22	12	9,5	15	12,27 €
PDM32-6-20	M6	32	13,5	22	12	9,5	20	12,27 €
PDM32-6-25	M6	32	13,5	22	12	9,5	25	12,94 €
PDM32-6-30	M6	32	13,5	22	12	9,5	30	12,94 €
PDM40-8-15	M8	40	13,5	26	14	10	15	15,39 €
PDM40-8-20	M8	40	13,5	26	14	10	20	15,82 €
PDM40-8-25	M8	40	13,5	26	14	10	25	16,15 €
PDM40-8-30	M8	40	13,5	26	14	10	30	16,45 €
PDM40-8-40	M8	40	13,5	26	14	10	40	17,21 €
PDM40-8-50	M8	40	13,5	26	14	10	50	17,57 €
PDM50-10-20	M10	50	19	32	18	12	20	20,69 €
PDM50-10-25	M10	50	19	32	18	12	25	20,97 €
PDM50-10-30	M10	50	19	32	18	12	30	21,33 €
PDM50-10-40	M10	50	19	32	18	12	40	21,79 €
PDM50-10-50	M10	50	19	32	18	12	50	22,09 €
PDM50-10-60	M10	50	19	32	18	12	60	22,45 €

Dimensions in mm

Detectable plastic palm grip

New

PDV Visually identifiable blue thermoplastic

- ***Ultramarine blue operating element for sensitive sectors***
- *In the event of breakage during production in sensitive sectors such as the food industry, plastic fragments are easily identified visually, enabling them to be removed quickly*
- *Materials :*
  Visually detectable thermoplastic (glass-fibre reinforced polyamide), EU10/2011 and FDA compliant (RAL5002 colour)
  Components in polished 316L stainless steel
- *Operating temperature: -20°C to +100°C*





Application

- *Food industry*
- *Pharmaceutical industry*
- *Packaging industry*


Info.

- *Food-grade materials*





Typical application



DISCOUNTS

Qty	1+	6+	10+	25+
Disc.	List	-5%	-10%	On request

Part Number	ØD	ØD1	ØD2	H	H2	H3	T	Price each 1 to 5
PDV25-5	M5	25	10	18	9	7	9	10,15 €
PDV32-6	M6	32	13,5	22	12	9,5	12	12,36 €
PDV40-6	M6	40	13,5	26	14	10	12	15,45 €
PDV40-8	M8	40	13,5	26	14	10	12	15,45 €
PDV50-8	M8	50	19	32	18	12	17	20,94 €
PDV50-10	M10	50	19	32	18	12	17	20,94 €

Dimensions in mm

New


Detectable plastic palm grip


Visually identifiable blue thermoplastic PDV

NEW !



- ***Ultramarine blue operating element for sensitive sectors***
- *In the event of breakage during production in sensitive sectors such as the food industry, plastic fragments are easily identified visually, enabling them to be removed quickly*
- *Materials :*
  Visually detectable thermoplastic (glass-fibre reinforced polyamide), EU10/2011 and FDA compliant (RAL5002 colour)
  Components in polished 316L stainless steel
- *Operating temperature: -20°C to +100°C*






Application

- *Food industry*
- *Pharmaceutical industry*
- *Packaging industry*

Info.

- *Food-grade materials*



Typical application

DISCOUNTS

Qty	1+	6+	10+	25+
Disc.	List	-5%	-10%	On request

Part Number	ØD	ØD1	ØD2	H	H2	H3	L	Price each 1 to 5
PDV25-5-10	M5	25	10,0	18	9	7,0	10	10,51 €
PDV25-5-15	M5	25	10,0	18	9	7,0	15	10,51 €
PDV25-5-20	M5	25	10,0	18	9	7,0	20	10,51 €
PDV32-6-10	M6	32	13,5	22	12	9,5	10	11,42 €
PDV32-6-15	M6	32	13,5	22	12	9,5	15	11,42 €
PDV32-6-20	M6	32	13,5	22	12	9,5	20	11,42 €
PDV32-6-25	M6	32	13,5	22	12	9,5	25	12,06 €
PDV32-6-30	M6	32	13,5	22	12	9,5	30	12,06 €
PDV40-8-15	M8	40	13,5	26	14	10,0	15	14,36 €
PDV40-8-20	M8	40	13,5	26	14	10,0	20	14,76 €
PDV40-8-25	M8	40	13,5	26	14	10,0	25	15,06 €
PDV40-8-30	M8	40	13,5	26	14	10,0	30	15,39 €
PDV40-8-40	M8	40	13,5	26	14	10,0	40	16,03 €
PDV40-8-50	M8	40	13,5	26	14	10,0	50	16,36 €
PDV50-10-20	M10	50	19,0	32	18	12,0	20	19,33 €
PDV50-10-25	M10	50	19,0	32	18	12,0	25	19,54 €
PDV50-10-30	M10	50	19,0	32	18	12,0	30	19,91 €
PDV50-10-40	M10	50	19,0	32	18	12,0	40	20,33 €
PDV50-10-50	M10	50	19,0	32	18	12,0	50	20,60 €
PDV50-10-60	M10	50	19,0	32	18	12,0	60	20,94 €

Dimensions in mm

Altri prodotti...


RHTtcss

Ruota alte temperature, fino a 200kg


UCFL_PBT

Supporto a flangia ovale con cuscinetto, Polimero e inox


BCM_TP

Spazzola cilindrica modulare, Filo in tampico


R204

Molla per stampi ISO10243, Medio


ADL_F

Anello di sollevamento, Inox


SSB

Ingranaggio conico inox, 1:1


UGH32

Unità di guida tipo H, Per martinetti Ø 32


PCLA_T

Maniglia a ripresa - maschio, Plastica


GE_ET_2RS

Snodo sferico, Cromo duro/PTFE con guarnizioni di tenuta


BAC110

Contenitore a becco, Contenitore


HBM

Guida su semi-binari, Boccola di regolazione


RPP

Piastra di giunzione per cinghia RPP, RPP14

Prodotti correlati


BEAS

Manopola, stella, antistatico


BEAS

Star shaped anti-static handle, Star, anti-static


BEAB

Manopola, stella, anti-bacterial


BEAB

Manopola, stella, antibactterico