Mounting feet with integrated castors

Offset castor

PDR

- ***Combines the advantages of a static mounting foot and a castor***
- *Use a hexagonal spanner to release the castor*
- *Castor protrudes 12.5mm when released*
- *Only for use on surfaces that are smooth (crevices less than 5mm) and horizontal (max slope 3°)*
- *Max static load 2,500 kg per foot*
- *Max load 200 kg per foot if used in movable mode*
- *Materials:*
  Base - Polyamide
  Sole - NBR rubber
  Threaded shaft - Chromed steel




Typical application


- *A vessel remains static whilst the product within is processed but once empty, can be moved for cleaning purposes.*

Advantages

- *Flexibility (1 item performs 2 functions)*
- *Less manœuvring to move a structure*
- *Time saving*



Retracting the castor



DISCOUNTS

Qty	1+	6+	10+
Disc.	List	-5%	On request

Part number	ØM	L	Load Castor fixed (static) (kg)	Load Castor free (dynamic) (kg)	Price each 1 to 5
With threaded shaft					
PDR100-16-50/RD	M16	50	2500	200	118,60 €
PDR100-16-100/RD	M16	100	2500	200	122,18 €
PDR100-20-75/RD	M20	75	2500	200	122,18 €
PDR100-20-125/RD	M20	125	2500	200	125,78 €
PDR100-24-75/RD	M24	75	2500	200	122,18 €
PDR100-24-125/RD	M24	125	2500	200	125,78 €
With 80x80mm mounting plate					
PDR100-80-80/RD	4x8.5mm holes		2500	200	122,18 €

Dimensions in mm

Altri prodotti...



Squadra di giunzione, PRF4590



Moschettone DIN5299 acciaio, Acciaio



Ingranaggio dritto PRESTAZIONE, Acciaio 35NCD6



Giunto elastico alluminio serie eco., Alluminio



Valigetta di guarnizioni toriche in nitrile, 3.00 x 2.00mm a 45.20 x...



Ingranaggio conico inox, 1:1



Impugnatura termoplastica a T, Con inserto maschiato



Tenditore rigido, Fisso



Distanziatore esagonale, Ottone



Manicotto a sfere autoallineante



Chiusura a leva, Con porta-lucchetto



Profilato alluminio standard, 45 x 45 mm

Prodotti correlati

Topball



Ruota di livellamento, Con foro centrale



Ruota di livellamento, Con piastra