Sliding profile

PGT

Plastic

- ***For square tube ⍁ 25 x 25***
- *Material: polyethylene*
- *Colour: black*




Accessories


- *Structural tube* **TUBE**
- *Support profiles* **PSP**

Info.


- **PGT25-D** *comprises 2 elements, top and bottom*




Top part



Profile type PGT-D **Bottom part**



Profile type PGT-S



Typical application

DISCOUNTS

Qty.	1+	5+	10+
Disc.	List	-5%	On request

Part number	Type	Length (mm)	Weight (kg/m)	Stock*	Price each 1 to 4
PGT25-S	Single	2000	0,53	✔	28,01 €
PGT25-D	Double	2000	0,85	✔	221,69 €

**Depending on availability - Dimensions in mm*

Altri prodotti...



DOG111

Motoriduttore DC 12V e 24V DC, da 1.5 a 6 Nm



BOXINS300

Inserto autofilettante, Box kit per materiali duri



RPP

Piastra di giunzione per cinghia RPP, RPP8



CDP

Boccola di posizionamento, Acciaio



BPFss

Supporto a flangia tonda a carico leggero inox, Inox



T10_30_AL

Puleggia dentata di posizionamento tipo T, Serie economica - T10 all...



DOMI80

Accessori di collegamento, Leva di serraggio



GAL_20

Rullo per trasportatore, Polietilene autolubrificato



HRV

Sistema di guida su binario a V Simple



ACLEPP

Angolare, 8 fori



HRV

Sistema di guida su binario a V Simple



NAST

Rotelle, Con anello interno

Prodotti correlati



TUBE25_25

Tubo quadrato, Alluminio



NCT

Giunto di collegamento, Ad angolo fisso



NCT

Giunto di collegamento, Ad angolo fisso



NCT

Giunto di collegamento, Ad angolo fisso