Idler sprocket for plate chain


PR880 For chain range 880 TAB

- **For use with CAP880T plate chains**
- Materials:
  Reinforced polyamide
  Stainless steel screws
- Operating temp.: -10°C to +120°C
- For dimensions and bore tolerances, please refer to technical pages

Advantage


- Two part design facilitates easy assembly

Easy assembly





Two part design



DISCOUNTS

Qty.	1+	5+	10+
Disc.	List	-5%	On request

Part number	No. of teeth	ØDE	ØDP	Bore ØA	Weight (kg)	Price each 1 to 4
PR880-12-25	12	147,2	147,21	25	0,39	25,38 €
PR880-12-30	12	147,2	147,21	30	0,39	25,38 €
PR880-12-35	12	147,2	147,21	35	0,39	25,38 €
PR880-12-40	12	147,2	147,21	40	0,39	25,38 €

Dimensions in mm

Altri prodotti...



BCM_MPBT

Spazzola cilindrica modulare, Filo poliestere PBT



SVG

Chiusura a leva regolabile, Corsa da 106,7mm a 121,4mm



CCLSS

Capocorda ad occhiello, Inox



PSPD18

Manopola a pressione, PVC nero



VAB

Vite a ricircolo di sfere al metro, Vite a sfere rullata, al metro



PO

Maniglia a ponte - Multi-settore, Foro cieco maschiato



RJA00_02

Guarnizione in gomma, Da agganciare



SME

Testa a snodo maschio, Inox / PTFE



HTD5M_25

Puleggia dentata di trasmissione tipo HTD, HTD5 Acciaio o



CSS

Snodo sferico, acciaio/acciaio autolubrificante



UGAC_UGET

Guida per cilindrico, Giunto per stelo filettato del



PF20

Riduttore a ruota e vite senza fine, fino a 5 Nm

Prodotti correlati



CAP880

Catena a tapparella, Stretta serie 880



PT880

Pignone di trazione, Serie 880



BAP25

Anello di bloccaggio, Ø25 - Ø40



BAP

Anello di bloccaggio, Ø10 - Ø20