Screen support for aluminium profile


PRFSCREEN Support with 4 axes of rotation


- ***Screen support on articulated arm***
- *Can be fixed in the slot or on the end of a* ***PRF4545*** *aluminium profile, or on a fixed support*
- *360°rotation on the vertical axis*
- *For screens conforming to VESA75 and VESA100 mounting standards*
- *Materials :*
  Removable VESA mounting plate - Steel/Plastics
  Screen holder - Cast aluminium, lacquered
  Support plate - Cast aluminium, lacquered
  Adapter - Cast aluminium, lacquered
  Cable cover - Black plastic
  Bearings and washers - Black plastic
  Zinc-plated steel screws



Advantages

- *Easy to install on an aluminium profile*
- *Adjusts in all directions for optimum visibility*
- *Careful finishing for maximum strength*





DISCOUNTS

Qty	1+	3+	5+
Disc.	Net	-5%	On request

Part N°	Carrying capacity (kg)	Weight (g)	Price each 1 to 2
PRF-SCREEN-4	2 - 10	2200	286,03 €

Altri prodotti...



Articulated fixable foot, pressed bolt-down base Ø 120, Ø 120



Ruota per vite senza fine, Bronzo



Morsetto incrociato, Montaggio e regolazione rapidi




Ingranaggio dritto acciaio, Acciaio 20NCD2



Antivibrante elastico cilindrico, Acciaio



Cinghia aperta al metro tipo T, T5 Poliuretano armatura in acciaio



Magnete, Magnete piatto con filettatura



Attrezzi per inserti filettati, Attrezzo di posa



Maniglia a ripresa, Zamak



Pistoncino a molla, Bloccabile - Inox



Dado trapezoidale, Bronzo - 2 filetti



Piedino antivibrante cilindrico, Inox

Prodotti correlati



Profilato alluminio standard, 45 x 45 mm



Profilato inox standard, 45 x 45 mm



Screen support, Basic support



Screen support, Support with 5 axes of rotation