
Base support plate

Plate with central hole

MiniTecPRFBM

- ***Base plate for attaching foot or lifting ring***
- *Fixing kit supplied*
- *Feet/lifting ring not supplied*
- *Material: grey powder covered steel*



Assembly

- *Fits in slot on profile*

Accessories

- **PR/PRS/PAT/PAM** *ranges of feet*

DISCOUNTS

Qty.	1+	50+	100+
Disc.	List	-5%	On request

Part number	For profile	Thickness (mm)	Weight (kg)	Stock*	Price each 1 to 49
PRF4590-BM10	PRF4590	15	0,164	✔	9,71 €
PRF4590-BM12	PRF4590	15	0,162	✔	9,71 €
PRF4590-BM16	PRF4590	15	0,160	✔	9,71 €
PRF4590-BM20	PRF4590	15	0,156	-	9,71 €

**Depending on availability - Dimensions in mm*

Altri prodotti...



Guida mini Drylin® N, Larghezza 27 mm



Tavola di posizionamento verticale manuale, 3kg



Guida lineare a rulli, Carello - da 9410 N a 101000 N



Perno autobloccante inox temprato ad anello, Con impugnatura ad



Calettatore di bloccaggio autocentrante acciaio, Con ghiera



Anello di sollevamento, Articolato - a saldare



Ingranaggio dritto acciaio, Acciaio 20NCD2



Guide telescopiche per montaggio in scanalatura, Estensione parziale



Martinetto a vite - Vite traslante, Vite



Rondella sferica - DIN6319, convessa



Braccio di reazione, Serraggio standard



Ruota per vite senza fine, Bronzo

Prodotti correlati



Profilato alluminio standard, 45 x 90 mm



Piede fissabile con snodo - poliammide, Ø 40