
Clamp for aluminium profile

PRFBR MiniTec

- ***Supplied with fixing kit***
- *Material:*
  Anodised aluminium





Use

- *Use the slots on two profiles to connect them at any angle*


Assembly

- *Attach the clamp to the slot of the first profile and then tighten the second*
- *No preparation required*





Typical application



DISCOUNTS

Qty.	1+	50+	100+
Disc.	List	-5%	On request

Part number	Type	Weight (kg)	Stock*	Price each 1 to 49
PRF-BR	Clamp	0,069	✔	8,90 €

**Depending on availability - Dimensions in mm*

Altri prodotti...


NRV

Morsetto incrociato, Montaggio e regolazione rapidi


PM4

Ruota per vite senza fine, Bronzo


GE1006

Chiusura a leva adattabile, Per aggancio in gola


UFX

Giunto elastico Uneflex®, economica


WS16

Binario Drylin® W, Binario


PAP


Maniglia e battuta per porta, Maniglia ergonomica


PARF110

Piede senza snodo, Piede snodato oscillante fissabile Ø110


RPC

Ruota, Poliammide


NSB

Supporto standard per manicotto chiuso a sfere, Chiuso - Lungo


HLC19

Rinvio angolare a dentatura spiroidale, Fino a 43Nm


S2B

Supporto corto per manicotto chiuso a sfere, Chiuso - Corto


SBF

Sealed flange bearing unit for Food Industry, cover

Prodotti correlati


PRF4545

Profilato alluminio standard, 45 x 45 mm