
Cable-carrier chain for aluminium profile

For profile PRF4545-G-3 MiniTec PRFCH

- ***Supplied in metre lengths, this chain simply clips together***
- *2 part fixing link required*
- *Material: black plastic*



Uses


- *For supporting and guiding cables/hoses on moveable structures such as trolleys*


Assembly

- **PRF4545-ACH** *links permit multiple chains to be joined to obtain the total length required*
- *Clip chains together to get the length desired*



Typical application





DISCOUNTS

Qty.	1+	5+	10+
Disc.	List	-5%	On request

Part number	Type	Length (mm)	Weight (kg)	Price each 1 to 4
PRF4545-CH	Cable-carrier chain	1000	0,341	40,82 €
PRF4545-ACH	Link	-	0,058	9,51 €

Dimensions in mm

Altri prodotti...



PLA

Magnete piatto, Magnete piatto



H0

Ingranaggio elicoidale ad assi incrociati a 90°, Acciaio 20NCD2



SER

Accessori per porte, Fermaporte a calamita



T10courroie

Cinghia di posizionamento T, T10 Poliuretano armatura in acciaio



CMM

Testa a snodo maschio DIN ISO12240-4, Acciaio / bronzo



WSSss

Gancio a S simmetrica, Inox



GP75

Chiusura a leva molla a trazione compensata, Standard (GP75)



LRX

Guida lineare a rulli, Carello - da 9410 N a 101000 N



MTTHR

Campanella tripla alta resistenza, alta resistenza



PTA40ssEB

Articulated foot whit sheet metal base Ø40, 3000N



PAMF80EB

Piede snodato con base stampata fissabile Ø80, Piede



VAB

Flanged nut for ball screw, For VAB ballscrew

Prodotti correlati