Nut for aluminium profile


PRFECL MiniTec

With tab


- ***Square nut with sprung tab***
- *Nut can be inserted at any point along the slot in a profile*
- *Material: zinc plated or stainless steel*
- ***Not sold individually, contact us for details***


Advantages

- *Allows parts to be added/removed easily*
- ***Sprung tabs allows the nut to be retained in place when using vertically positioned profiles***



steel or stainless steel





Very simple positioning

DISCOUNTS

Qty.	1+	50+	100+
Disc.	List	-5%	On request

Part number Steel	Part number Stainless steel	ØT	Stock* Steel	Price each 1 to 49 Steel	Price each 1 to 49 Stainless steel
PRF-ECL-M3	PRF-ECL-M3/SS	M3	✔	0,73 €	2,25 €
PRF-ECL-M4	PRF-ECL-M4/SS	M4	✔	0,73 €	2,25 €
PRF-ECL-M5	PRF-ECL-M5/SS	M5	✔	0,73 €	2,25 €
PRF-ECL-M6	PRF-ECL-M6/SS	M6	✔	0,73 €	2,25 €
PRF-ECL-M8	PRF-ECL-M8/SS	M8	✔	0,73 €	2,25 €

**Depending on availability - Dimensions in mm*

Altri prodotti...



UGH16

Unità di guida tipo H, Per martinetti Ø12 e Ø16



UTKpwc

Guida lineare Utilitrack®, Ruota a V - rivestimento polimero



HW_HT

Guida su semi-binari, Binario



PRF-SCREEN-4

Screen support, Support with 4 axes of rotation



AC156-157

Riscontro per chiusura a leva rigida ad anello, 25.5mm



ZG0

Ingranaggio dritto in plastica, Plastica lavorata (delrin)




AT5M_AT10M

Cinghia aperta al metro tipo AT, AT5 Poliuretano armatura in acciaio



PCS_PA6

, 9.525mm (DIN 06B-1)



ZR

Cremagliera in plastica, Delrin



GPLss

Scovolo, inox



PTA80

Piede snodato con base stampata Ø80, 10000N



G-ECO

Ingranaggio dritto acciaio - serie ECO, Acciaio C45

Prodotti correlati



PRF4545

Profilato alluminio standard, 45 x 45 mm



PRF_FIX_ANG

Fissaggio, Fissaggio angolare



ACL-PR

Elementi di giunzione, Collegamento a 90°



ACL-PR

Elementi di giunzione, Collegamento a 90°