
Fastener for aluminium profile

Angular joint

MiniTecPRF


FIXANG


- ***Creates an angular joint between the end of a profile and the side of a second.***
- *Fixing kit supplied*
- *Material: electroplated steel*




Assembly


- *Drill a Ø10.2mm in the centre of the side of the horizontal profile*
- *Drill a Ø8.2 mm at a distance A (see table) from the end of the angled profile*
- *Insert the angled fastener in the Ø10.2mm hole*
- *Position the PRF-ECL-M8 nut in the slot at Ø8.2 hole*
- *Tighten the joint by means of the M8 grubscrew*






α	25°	30°	35°	40°	45°	50°	55°	60°	65°	70°	75°	80°	85°
A(mm)	21	24	26	28	29	30	30,5	31	31,5	32	32	32	32







DISCOUNTS

Qty.	1+	50+	100+
Disc.	List	-5%	On request

Part number	Weight (kg)	Stock*	Price each 1 to 49
PRF-FIX-ANG	0,051	✔	10,92 €

**Depending on availability - Dimensions in mm*


Altri prodotti...



Unità di guida per cilindrico, Cuscinetto corto




Riduttore a ruota e vite senza fine, fino a 196 Nm




Riduttore a ruota e vite senza fine, fino a 8.80 Nm



Piede fissabile con base lamiera Ø80, Ø 80



Ingranaggio conico - Acciaio 60C40, 1:1



Panel accessories, Guarnizione - Ø 2mm



Rotella per profilo alluminio, Albero per guida



Catena dritta a maglie lunghe, Acciaio zincato



Riduttore inox a ruota e vite senza fine, fino a 152 Nm



Volantino zigrinato, Zigrinato



Vite senza fine, Acciaio temprato



Riduttore inox a ruota e vite senza fine, fino a 80 Nm

Prodotti correlati



Fissaggio, Dado quadrato con linguetta - Acciaio



Profilato inox standard, 45 x 45 mm



Fissaggio, universale