

Fastener for aluminium profile

Stock

PRF MiniTec

Standard fastener

FIXSTD

Profile assembly




- Suitable for loads up to 18000N
- Can be used to securely join all profile types
- Forms very efficient anti-twist joint
- Materials:
 - M8x50mm CHC screw: electroplated steel
 - Locking plate: electroplated steel

Uses

- For heavy or vibrating loads

Assembly

- Drill a stepped hole ($\varnothing 9$, $\varnothing 15$) at the required position
- Slide the screw locking plate in the slot
- Pass the end of the screw through the first profile (1), the locking plate and then into the central hole of the second profile (2) which was previously tapped (M8 x 25mm) and tighten.



DISCOUNTS

Qty.	1+	50+	100+
Disc.	List	-5%	On request

Part number	Load (N)	For profile	Tightening torque (Nm)	Weight (kg)	Stock*	Price each 1 to 49
PRF-FIX-STD	18000	All types of PRF profile	20	0,03	✓	1,96 €

*Depending on availability - Dimensions in mm

Altri prodotti...



PR5100
Piede snodabile tutto inox Ø100, Ø 100



RCX-6
Rondella sferica - DIN6319, concava



LVT
Mini martinetto motorizzato 2A, 2 ampere



PTKFss
Piede fissabile speciale agroalimentare, Stainless steel - 3-A



AT5-16ECO
Puleggia dentata di posizionamento tipo AT, Serie economica - AT5 al...



BAN
Connettore / supporto per profili alluminio, Regolabile



PR125
Piede fissabile con snodo - poliammide, Ø 123



RFK58B
Riduttore ipoide inox, fino a 500 Nm



LRR
Chiavistello con perno prismatico, Gancio



PLN
Distanziatore cilindrico, termoplastica



PM4
Coppia ruota e vite senza fine, Acciaio temprato



DKONSL
Piedino antivibrante conico silicone, Fissaggio maschio

Prodotti correlati




PRF1932
Profilato alluminio standard, 19 x 32 mm



PRF4545
Profilato inox standard, 45 x 45 mm



PRF_FIX_UNI
Fissaggio, universale



PRF4545r90
Profilato alluminio standard, 45 x 45 mm - R90°