
Lip seal for panel

PRFJL MiniTec — For 2mm thick panels

- Material: black EPDM
- **Seal sold by the metre**



Uses


- For supporting and sealing 2mm thick panels in profile slots
- Should not be used with acrylic or polycarbonate panels

Assembly


- Place the panel in the profile slot
- Insert the lip seal
- Press seal into place with suitable blunt tool
- For panels thinner than 2mm, use 2 **PRF-JL-6** seals on either side of the panel instead.

Info.

- Max length available 200m
- Panels: Add 25mm to height and width of aperture to ensure panel will be supported correctly



Assembly example



DISCOUNTS

Qty.	1+	50+	100+
Disc.	List	-5%	On request

Part number	Type	Weight (kg/m)	Price per metre
PRF-JL-2	Lip seal	0,092	3,17 €

Dimensions in mm

Altri prodotti...



Sfera portante Agro,



Supporto per sensore Ø12, Ø12



Vite trapezoidale acciaio, Acciaio semiduro - 1 filetto



Ingranaggio conico in plastica stampata, 1:1



Vite di giunzione metallo/legno, Acciaio




Ingranaggio dritto ottone, Ottone CuZn39Pb3



Forcella serie corta, Corta acciaio



Chiusura a leva, Standard



Attuatore lineare a motore 4A, 4 ampere



Pistoncino a molla, acciaio classe 5.8



Perno autobloccante, Boccole di fissaggio con flangia ovale



Manicotto chiuso a sfere di precisione, Economica

Prodotti correlati



Profilato alluminio standard, 45 x 45 mm