
Lip seal for panel

For 6mm thick panels

MiniTecPRFJL

- Material: black EPDM AGV
- ***Seal sold by the metre***



Uses


- For supporting and sealing 6mm thick panels in profile slots
- Can be used with plexiglass or polycarbonate panels
- Can also be used to support panels thinner than 2mm by using a seal on each side

Assembly


- Place the panel in the profile slot
- Insert the lip seal
- Press seal into place with suitable blunt tool

Info.

- Max length available 200m
- Panels: Add 25mm to height and width of aperture to ensure panel will be supported correctly



Assembly example



DISCOUNTS

Qty.	1+	50+	100+
Disc.	List	-5%	On request

Part number	Type	Weight (kg/m)	Price per metre
PRF-JL-6	Lip seal	0,033	1,58 €

Dimensions in mm

Altri prodotti...


CHMR63

Riduttore a ruota e vite senza fine, fino a 196 Nm


ASL

Anello di sollevamento, a 45° a saldare


CFS

Perno folle mini, Miniatura


VQTplqp

Chiusura ¼ di giro – Piastra di bloccaggio, Montaggio con controd...


PSG1

Ingranaggio dritto di precisione, Acciaio 35NCD6 pretrattato


BPPE

Sfera portante, Leggero


SHNbr

Dado esagonale - DIN934, Ottone


PGNT


Impugnatura termoplastica a T, Con perno filettato


CHMR30

Riduttore a ruota e vite senza fine, fino a 28 Nm


UGAC_UGET

Guida per cilindrico, Giunto per stelo filettato del


MET

Cuscinetto cilindrico , Bronzo autolubrificante


NCT

Giunto di collegamento, Ad angolo fisso

Prodotti correlati


PRF4545

Profilato alluminio standard, 45 x 45 mm