Caster for use with aluminium profile

Without brake

MiniTecPRFROUL

- ***Supplied with fixing kit***
- *Materials:*
  Casing : black polyamide
  Double wheel: black polyamide
- *Max. load: 30kg*




Uses


- *Light mobile tables*
- *Wheeled filing cabinets*
- *Furniture*

Assembly

- *Tap (M8) the central hole of the profile and screw on the caster*



Typical application



DISCOUNTS

Qty.	1+	50+	100+
Disc.	List	-5%	On request

Part number	Type	Weight (kg)	Price each 1 à 49
PRF-ROUL	Caster without brake	0,076	7,89 €

**Depending on availability*

Altri prodotti...



QNJ

Cuscinetto a singola corona di rulli cilindrici, Anello interno fiss...



HG8-ECO

Ingranaggio dritto acciaio, Acciaio C45



DB

Ingranaggio conico - Acciaio 60C40, 2:1



CLM

Attacco per forcella, Corta acciaio



AT10-50ECO

Puleggia dentata di posizionamento tipo AT, Serie economica - AT10 a...



BCA

Ghiera scanalata cilindrica in acciaio, Acciaio



PRF_FIX_UNI

Fissaggio, universale



PRF_BASE

Elementi di ancoraggio, Basamento



TK_UUOP

Manicotto a sfere autoallineante



Q6

Cuscinetto radiale a sfere, Acciaio



RFK38C

Riduttore ipoide inox, fino a 200 Nm



PSG2S

Ingranaggio dritto di precisione, Inox 303

Prodotti correlati



PRF4545

Profilato alluminio standard, 45 x 45 mm