
Bracket for aluminium profiles

Stock


PRF MiniTec — Support bracket

- ***Can be used for all types of construction, recommended for use when adding profiles to existing structures***
- *Use to reinforce structures*
- *Can be positioned anywhere along the profile length*
- *For heavy loads, use multiple brackets*
- *Fixing kit supplied*
- *Material: grey powder coated aluminium GD*



Accessories

- *Nut with sprung tab* **PRF-ECL**




Special application


- **PRF25-E** *bracket has a centred section that aligns along profile slot to prevent twisting*

Info.


- **Given for applications using two brackets; when using a single bracket, maximum load is reduced, please contact us for details*



PRF45-E



PRF25-E



PRF19-E

DISCOUNTS

Qty.	1+	50+	100+
Disc.	List	-5%	On request

Part number	Max. load* (N)	Max. torque (Nm)	For profile	Tightening torque (Nm)	Stock*	Price each 1 to 49
PRF19-E	1200	400	PRF19, PRF32	20	✔	3,98 €
PRF25-E	1200	400	PRF19, PRF32, PRF45	20	✔	4,57 €
PRF45-E	1200	400	PRF45	20	✔	3,98 €

**Depending on availability - Dimensions in mm*

Altri prodotti...


FUSS

Ghiera autofrenante per cuscinetto, Ghiera autofrenante - rondella i...


BS2

Panamech, Multi-Beam, Alluminio - con vite a pressione


CHINV

Cerniera invisibile, Invisibile - Apertura 90°


PTAF100-PAMF100

Piede fissabile con base lamiera Ø100, Ø 100


SH0

Ingranaggio elicoidale ad assi paralleli, Acciaio 20NCD2


PSG1S

Ingranaggio dritto di precisione, Inox 316


DB

Ingranaggio conico in acciaio, 2:1


BABS303

Perno autobloccante inox 303, Inox 303


LWL

Guida lineare a sfere - Sfere inox, Carello -


BSM

Pressore a molla con esagono incassato,


OP3

Indicatore di posizione digitale (N. di giri), 4


PM3

Vite senza fine, Acciaio non temprato

Prodotti correlati


PRF_ECL_

Fissaggio, Dado quadrato con linguetta - Acciaio


PRF_VTM

Fissaggio, Vite testa martello