
New Dual lock for use on aluminium profile

Quick fitting, self blocking door lock

PRFSRAD

- **Door or trap lock for structures assembled from PRF4545 aluminium profiles**
- Mounts on central support and allows 2 doors to be locked separately
- Material: Die cast aluminium housing with black finish






No machining required

Advantages


- Easy to mount from the front using M6 CHC screws
- No drilling required
- Security feature: Cannot be removed when in locked position

Accessories

- **CHC6-16** screws and **PRF-ECL-M6** channel mounting nuts not supplied



NEW!







More aesthetic and more economical

DISCOUNTS

Qty	1+	2+	5+
Disc.	List	-5%	On request

Part number	Type	For slot N	Weight (g)	Price each
PRF-SRAD-78-A	With universal key	8/10	235,5	62,28 €
PRF-SRAD-78-B	With individual key	8/10	235,5	62,28 €

Dimensions in mm

Altri prodotti...



Guida su semi-binari, Ruota



Distanziatore esagonale, Inox 303



Distanziatore esagonale, Inox 303




Articulated fixable foot, pressed bolt-down base Ø 120, Ø 120




Dado piastrina, Per scanalatura a T



Pistoncino a molla, Per lamiera



Cinghia aperta al metro tipo RPP, RPP14 Poliuretano armatura in acci...



Attuatore lineare a motore 2A, 2 ampere



Volantino a 6 lobi, Tecnopolimero - Acciaio



Piede snodato con base stampata Ø50, 4000N



Ingranaggio elicoidale ad assi paralleli, Plastica lavorata



Snodo sferico, acciaio/acciaio e guarnizioni di tenuta

Prodotti correlati



Fissaggio, Dado quadrato con linguetta - Acciaio



Profilato alluminio standard, 45 x 45 mm