Emergency release button

New

PRFBOU — For use with profile locks

- ***Emergency release button allows security doors fitted with PRF-SRA-CAP locks to be opened***
- *Secured using CHC M6 screws*
- *Materials:*
  Button: glass fibre reinforced PA nylon
  Plate: chromed steel
- *Working temp range: -20° to 55 °C*






Typical application

Advantages

- *Ideal for opening the door from the inside if there is a risk of an operator becoming trapped*
- *Can be mounted on 30, 40, 45 or 50 mm section profiles*
- *Ideal accessory for the* ***PRF-SRA-CAP*** *lock*

Accessories

- ***PRF-ECL-M6*** *screws*



DISCOUNTS

Qty	1+	2+	5+
Disc.	List	-5%	On request

Part number	Weight (g)	Price each
PRF-BOU-URG	110,8	30,90 €

Dimensions in mm

Altri prodotti...



QNUP

Cuscinetto a singola corona di rulli cilindrici, Anello interno con ...



EV

Terminale rapido inox per cavi,




GE32

Chiusura a leva rigida ad anello, Standard




LVT

Mini martinetto motorizzato 2A, 2 ampere



GALRUB

Rullo per trasportatore, Caucciù



MEFC

Cuscinetto a collare , Lega di ferro FP20 autolubrificante METAFRAM



CHB

Riduttore a ruota e vite senza fine, fino a 22 Nm



ACLRP

Rullo per profilati, Con cuscinetto a sfere



BTCW

Tappo inox per tubo quadrato, A saldare



UGH25

Unità di guida tipo H, Per martinetti Ø25



BOX-CSss

Fascette di serraggio, Valigetta di fascette inox



PARF110

Piede senza snodo, Piede snodato oscillante fissabile Ø110

Prodotti correlati



PRF4545

Profilato alluminio standard, 45 x 45 mm