Conical flexible shaft handle Ø20

New


PSPE20

For shafts Ø6 to Ø12

Conical handle
- *Smooth blind hole*
- *Working T°: 0°C to +70°C*
- *Material:*
  Black PVC

Assembly
- *Fit using a mallet, no adhesive required*





DISCOUNTS

Qty	1+	60+	100+	200+
Disc.	List	-5%	-10%	On request

Part number	ØD	ØD1	ØT	L	P	Weight (g)	Price each 1 to 59
PSPE20-43-6	20	14	6	43	40	11	1,78 €
PSPE20-43-7	20	14	7	43	40	10	1,68 €
PSPE20-43-8	20	14	8	43	40	10	1,62 €
PSPE20-43-10	20	14	10	43	40	9	1,56 €
PSPE20-43-12	20	14	12	43	40	8	1,50 €

Dimensions in mm

New

Conical flexible shaft handle Ø22


For shafts Ø7 to Ø14


PSPE22

Conical handle
- *Smooth blind hole*
- *Working T°: 0°C to +70°C*
- *Material:*
  Black PVC

Assembly

- *Fit using a mallet, no adhesive required*





DISCOUNTS

Qty	1+	60+	100+	200+
Disc.	List	-5%	-10%	On request

Part number	ØD	ØD1	ØT	L	P	Weight (g)	Price each 1 to 59
PSPE22-60-7	22	17	7	60	58	24	2,82 €
PSPE22-60-8	22	17	8	60	58	23	2,63 €
PSPE22-60-9	22	17	9	60	58	23	2,54 €
PSPE22-60-10	22	17	10	60	58	22	2,48 €
PSPE22-60-12	22	17	12	60	58	21	2,36 €
PSPE22-60-14	22	17	14	60	58	20	2,30 €

Dimensions in mm

Flexible tube handle

New Stock

PSPD18

For tubes Ø12 to Ø22


Knurled cylindrical handle
- *Smooth blind hole*
- *Working T°: 0°C to +70°C*
- *Material:*
  Black PVC

Assembly
- *Fit using a mallet, no adhesive required*


Advantages
- *Ergonomic handle for excellent grip*



NUOVO !



Typical application



DISCOUNTS

Qty	1+	60+	100+	200+
Disc.	List	-5%	-10%	On request

Part number	L	ØT	ØC	P	Weight (g)	Stock*	Price each 1 to 59
PSPD18-118-12	118	12	28	113	52	✔	4,31 €
PSPD18-118-14	118	14	28	113	45	-	4,00 €
PSPD18-118-16	118	16	28	113	40	✔	3,61 €
PSPD18-118-18	118	18	28	113	35	✔	3,24 €
PSPD18-118-20	118	20	28	113	28	✔	2,48 €
PSPD18-118-21	118	21	28	113	26	-	2,30 €
PSPD18-118-22	118	22	28	113	22	✔	2,11 €
PSPD18-118-22L	118	22	28	113	19	-	2,17 €

**Depending on availability - Dimensions in mm*

Stock New

Flexible tube handle

For tubes Ø18 and Ø22

PSPD40

Knurled cylindrical handle
- *Smooth blind hole*
- *Working T°: 0°C to +70°C*
- *Material:*
  Black PVC





Assembly

- *Fit using a mallet, no adhesive required*

Advantages

- *Ergonomic handle for excellent grip*





Typical application

DISCOUNTS

Qty	1+	60+	100+	200+
Disc.	List	-5%	-10%	On request

Part number	L	A	B	ØT	P	Weight (g)	Stock*	Price each 1 to 59
PSPD40-112-18	112	26	40	18	106	49	✔	4,68 €
PSPD40-112-22	112	26	40	22	106	47	✔	4,68 €


**Depending on availability - Dimensions in mm*

Flexible tube handle

PSPT

For Ø18 - Ø33 tubes

- ***Tube handle with collar***
- *Smooth interior*
- *Material:*
  Black PVC




NUOVO !

Assembly


- *Fit using a mallet, no adhesive required*

Advantages

- *Resists oil, shocks and low temperatures*



Typical application



DISCOUNTS

Qty	1+	60+	100+	200+
Disc.	List	-5%	-10%	On request

Part number	Tube ØT	L	ØD	ØD1	P	Weight (g)	Stock*	Price each 1 to 59
PSPT18-115	18-19	115	31	44	110	62	✔	3,22 €
PSPT20-115	20-21	115	31	44	110	56	✔	2,84 €
PSPT22-115	22-23	115	31	44	110	46	✔	2,47 €
PSPT24-125	24-25	125	36	49	120	72	✔	3,67 €
PSPT26-125	26	125	36	49	120	60	✔	3,22 €
PSPT27-125	27-28	125	36	49	120	50	✔	3,10 €
PSPT29-125	29	125	36	49	120	50	✔	3,10 €
PSPT30-130	30	130	42	51	125	92	✔	3,67 €
PSPT33-130	33	130	42	51	125	74	✔	3,28 €

**Depending on availability - Dimensions in mm*