
Drive sprocket for plate chain

For chain ranges 821 and 805 — PT821

- ***For driving CAP821 and CAP805 plate chains***
- *With bore and keyway*
- *Materials:*
  Reinforced polyamide
  Stainless steel screws
- *Operating temp.: -10°C to +120°C*
- *For dimensions and bore tolerances, please refer to technical pages*




Advantage

- *Two part design facilitates easy assembly*

Easy assembly



Two part design



DISCOUNTS

Qty.	1+	5+	10+
Disc.	List	-5%	On request

Part number	No. of teeth	ØDE	ØDP	Bore ØA	Weight (kg)	Price each 1 to 4
PT821-25-30	25	153	153,2	30	0,9	70,12 €
PT821-25-35	25	153	153,2	35	0,9	70,12 €
PT821-25-40	25	153	153,2	40	0,9	70,12 €
PT821-25-45	25	153	153,2	45	0,9	70,12 €

Dimensions in mm

Altri prodotti...



CFF

Testa a snodo femmina DIN ISO12240-4, Acciaio / bronzo



EBM

Cavallotto in acciaio, Acciaio



KB_OP

Manicotto a sfere di precisione, Di precisione - acciaio



PSG15

Ingranaggio dritto di precisione, Acciaio 20NCD2 cementato temprato



G01

Giunto cardanico semplice, Sollecitazioni normale



SSDB

Ingranaggio conico inox, 2:1



HTD14M_55

Puleggia dentata di trasmissione tipo HTD, HTD14 Ghisa o Acciaio



GLT3-76

Guide telescopiche acciaio, Estensione totale



BLOC

Accessori per porte, Arresto per porta



PCP

Kit connettori per portacellule, Pre-



HSS

Vite a spalla di precisione ISO7379,



CHAuss

Cerniera ad avvitare, 270°

Prodotti correlati



CAP821

Catena a tapparella dritta, Larga serie 821



CAP805

Catena a tapparella dritta, Larga serie 805