Adjustable furniture foot

New

PTCR

For square tube

Furniture foot with simple height adjustment
- *For square tubes 20x20mm to 50x50mm*
- *Turn to adjust height*
- *Working T° -30°C to +80°C*
- *Material:*
  Thermoplastic PA12 black





Advantages
- *Easy height adjustment*
- *Easy to install in the tube by pressure mounting*

Info
- *Not sold individually, please contact us for details*

NUOVO !

Example of use





DISCOUNTS

Qty	1+	60+	100+	200+
Disc.	List	-5%	-10%	On request

Part number	C	E	A	B	ØM	F	L	H	S		Price each 1 to 59
PTCR20-M10	20	20	5	4	M10	24	16,7	-	1,5 - 2	-	1,92 €
PTCR25-M16	25	24	5	5	M16	22	20	34,5	1,5 - 2	✔	2,12 €
PTCR30-M22	30	28	5	5	M22	20	19,5	45,5	1,5 - 2	✔	2,00 €
PTCR35-M22	35	28	5	5	M22	21,5	29,3	34,5	1,5 - 2	✔	3,10 €
PTCR40-M22	40	28	5	5	M22	21,5	29,3	34,5	1,5 - 2	✔	3,55 €
PTCR50-M30	50	41	5	5	M30	28	29,3	45,5	1,5 - 2	-	4,81 €

Dimensions in mm

Stainless steel telescopic furniture foot

With threaded stud

PTMR


Furniture foot with simple height adjustment
- *Turn to adjust height*
- *Materials:*
  Stainless steel foot 304
  Glass fibre reinforced nylon internal thread
  Anti-slip pad in black PVC


Advantages


- *Easy height adjustment*
- *When washing, the water flows over the outer part of the foot*



NUOVO !







DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc.	List	-5%	-10%	-15%	On request

Part number	ØD	ØD1	H	H1	ØF	Static load (N)		Price each 1 to 5
PTMR30-40-M10	30	40	80/110	67	M10x15	3000	-	21,82 €
PTMR44-56-M10	44,5	56,5	130/180	85	M10x30	5000	-	27,11 €
PTMR56-64-M10	56,5	64	130/180	85	M10x30	8000	-	29,84 €

Dimensions in mm

Stainless steel telescopic furniture foot Sta

PTMC


With square plate


Furniture foot with simple height adjustment
- *Turn to adjust height*
- *Materials:*
  Stainless steel foot 304
  Glass fibre reinforced nylon internal thread
  Anti-slip pad in black PVC

Advantages
- *Easy height adjustment*
- *When washing, the water flows over the outer part of the foot*




NUOVO !





Example of use: metal cabinet



DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc.	List	-5%	-10%	-15%	On request

Part number	ØD	ØD1	H	H1	K	N	Static load (N)		Price each 1 to 5
PTMC44-56-82	44,5	56,5	130/180	85	82	65	5000	-	31,86 €
PTMC56-64-82	56,6	64	130/180	85	82	65	8000	-	34,49 €

Dimensions in mm