

- "Teknohygienic" swivelling foot

- Materials:

Base: stainless steel 304

Stem: stainless steel 304

Sole: NBR rubber Shore hardness 90°


Advantages

- The 3-A standard designates products that are designed for the dairy, food and pharmaceutical industries where strict hygiene rules apply.
- Smooth finished foot with a wiper seal between the stem and the nut and around the swivel to prevent accumulation of dirt or retention of water
- Suitable for cleaning with water or chemicals
- USDA approved

For the food industry

stainless steel

Avoids water retention



DISCOUNTS

Qty	1+	6+	10+
Disc.	List	-5%	On request

Part number	ØM	Adjustable range E	A	B	ØD	SW	ØD1	ØD2	G	CH	H1	H2	H3	Static load (N)	Price each 1 to 5
PTK80-16-140/SS	M16	45	53	140	80	13	24	60	25	20	193	114	159	20000	82,47 €
PTK80-16-190/SS	M16	70	53	190	80	13	24	85	25	20	243	139	209	20000	99,00 €
PTK80-20-140/SS	M20	45	53	140	80	17	30	60	25	26	193	114	159	20000	86,60 €
PTK80-20-142/SS	M20	55	53	142	80	17	30	70	25	26	195	123	178	20000	89,47 €
PTK80-20-190/SS	M20	70	53	190	80	17	30	85	25	26	243	139	209	20000	99,90 €
PTK80-24-140/SS	M24	45	53	140	80	20	35	60	25	30	193	114	159	20000	94,15 €
PTK80-24-190/SS	M24	70	53	190	80	20	35	85	25	30	243	139	209	20000	106,73 €
PTK100-16-140/SS	M16	45	56	140	100	13	24	60	28	20	196	117	162	25000	86,42 €
PTK100-16-190/SS	M16	70	56	190	100	13	24	85	28	20	246	142	212	25000	102,96 €
PTK100-20-140/SS	M20	45	56	140	100	17	30	60	28	26	196	117	162	25000	90,56 €
PTK100-20-190/SS	M20	70	56	190	100	17	30	85	28	26	246	142	212	25000	103,84 €
PTK100-24-140/SS	M24	45	56	140	100	20	35	60	28	30	196	117	162	25000	98,10 €
PTK100-24-190/SS	M24	70	56	190	100	20	35	85	28	30	246	142	212	25000	110,69 €
PTK100-30-135/SS	M30	40	56	135	100	26	42	60	28	36	191	117	157	25000	107,80 €
PTK100-30-185/SS	M30	65	56	185	100	26	42	85	28	36	241	142	207	25000	117,85 €

Dimensions in mm

Fax **0 825 88 6000**
Service 0,15 € / min
+ prix appel

Altri prodotti...



NPR
Morsetto porta
catarifrangente,



RPCplss
Ruota fissa con
piastra, Inox -
Poliammide




SLVVlok
Bloccaggio a leva, A
leva verticale / base
verticale



M0
Coppia ruota e vite
senza fine , Acciaio
non temprato



CHTRB
Riduttore a rinvio
angolare a L o a T,
fino a 4,7 Nm



CRM
Cremagliera in nylon
stampato, Nylon



CNA-CNG
Staffa di montaggio
per molla a gas,
Staffa di montaggio a
squadra p...




SHW
Rondella semplice ,
Inox A2



PCS62
Pignone a catena -
acciaio, 15.875 (DIN



GFX
Giunto a dentatura
bombata serie



TBV
Tavola di
posizionamento



BAC105
Contenitore a becco,
8mm

Prodotti correlati



PTKFss
Piede fissabile
speciale
agroalimentare,
Stainless steel - 3-A

stand...



Piede snodato con
base stampata Ø80, Ø
80



Piede snodato con
base stampata Ø80, Ø
80



Piede snodato con
base stampata Ø100,
Ø 100