
Suction finger

New Alu

PV1R — Single rotation axis


- **Allows vacuum suction cups to be integrated into a handling system**
- Materials :
  Aluminium
  Screws : steel




Advantages

- Infinitely variable angle of adjustment
- Easy, flexible mounting

NEW !





Typical application

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØA	B	ØC	ØD	L	M	F	N	Weight (g)	Price each 1 to 9
PV20-1/8-50/1R	20	15	G1/8"	G1/8"	50	47	20	41	72	47,53 €
PV20-1/8-100/1R	20	15	G1/8"	G1/8"	100	47	20	41	87	49,57 €
PV20-1/8-150/1R	20	15	G1/8"	G1/8"	150	47	20	41	103	51,60 €
PV20-1/4-50/1R	20	15	G1/4"	G1/4"	50	49	25	43	93	48,55 €
PV20-1/4-100/1R	20	15	G1/4"	G1/4"	100	49	25	43	106	50,59 €
PV20-1/4-150/1R	20	15	G1/4"	G1/4"	150	49	25	43	123	52,62 €

Dimensions in mm

Altri prodotti...



EHD06

Riduttore coassiale, da 8 a 19 Nm



AT5M_AT10M

Cinghia aperta al metro tipo AT, AT5 Poliuretano armatura in acciaio



PTA50

Piede snodato con base stampata Ø50, 4000N



HLUMss

Impugnatura girevole, Inox 316



GP

Chiusura a leva molla a trazione compensata, Standard



INS100

Inserto auto-maschiante a passo grosso, Filetto largo



CLR

Staffa di montaggio per molla a gas, Staffa di montaggio per forcell...




AT10courroie

Cinghia di posizionamento AT, AT10 Poliuretano armatura in acciaio



LRR

Chiavistello con perno prismatico, Gancio



NSB

Supporto standard per manicotto chiuso a



D19_D29

Molla di compressione al metro acciaio, al



M0

Vite senza fine , Acciaio temprato

Prodotti correlati



PV2R

Braccio portaventosa orientabile, Serraggio rinforzato