

- Allows vacuum suction cups to be integrated into a handling system

- Materials :



Aluminium

Screws : steel


Advantages

- Infinitely variable angle of adjustment
- Easy, flexible mounting

NEW!



PV20-1/8-50/1R



BAN20/U

Typical application


DISCOUNTS

Qty	1+	10+	30+
Disc.	List -5%	On request	

Part number	ØA	B	ØC	ØD	L	M	∇F	N	Weight (g)	Price each 1 to 9
PV20-1/8-50/1R	20	15	G1/8"	G1/8"	50	47	20	41	72	47,53 €
PV20-1/8-100/1R	20	15	G1/8"	G1/8"	100	47	20	41	87	49,57 €
PV20-1/8-150/1R	20	15	G1/8"	G1/8"	150	47	20	41	103	51,60 €
PV20-1/4-50/1R	20	15	G1/4"	G1/4"	50	49	25	43	93	48,55 €
PV20-1/4-100/1R	20	15	G1/4"	G1/4"	100	49	25	43	106	50,59 €
PV20-1/4-150/1R	20	15	G1/4"	G1/4"	150	49	25	43	123	52,62 €

Dimensions in mm

Altri prodotti...




ACLBT5

Sistema di chiusura per profili alluminio, Squadra per blocca porta ...



RJA11_27

Guarnizione in gomma, Diverso dall'aggancio



KS

Chiavetta in barre, Inox - in barre



NTMdl

Grano punta in delrin, punta in delrin



NDS20

Connettore di serraggio, Parallela



RURt

Ruota girevole a foro centrale, Poliuretano - Mozzo alluminio (Ultra...



PRF1932

Profilato alluminio standard, 19 x 32 mm



PT881

Pignone di trazione, Serie 881



AT5P_AT10P

Piastra di giunzione per ghiaia AT, AT10



CHAFR-MINI

Cerniera, A frizione



RBGpl

Ruota girevole a doppio bloccaggio,



WW10

Guida Drylin® W, Carrello

Prodotti correlati



PV2R

Braccio portaventosa orientabile, Serraggio rinforzato