
Locking castor with mounting plate

For loads up to 1000kg


RIM

- **A combination of a swivel castor and an adjustable locking support**
- Used to easily support and moving machines or other heavy equipment and then positioning them in a very stable manner.
- Installation starts by lowering the locking support using a nut.
- With the wheel no longer resting on the ground, the supported unit can be levelled despite any irregularities in the floor.
- Operating temperature range: -30 to +80°C



Materials

- Polyamide central control cross nut
- Anti-skid rubber mount allowing absorption of vibration and noise
- Body: Moulded cast aluminium body, hammered ivory paint finish
- Swivel system provided by 2 ball rings
- Mounting plate has a threaded central hole, threaded rod and nut supplied.
- Wheel: Black polyamide Shore D 70





DISCOUNTS

Qty	1+	5+	14+
Disc.	List	-5%	On request

Part number	ØA	B	H1	H2	L	M	ØT	Swivel interference ØK	Load (kg)	Price each 1 to 5
RIM42-60/PLE	42	20	71	81	55x55	42x42	6,5	84	60	44.77 €
RIM50-280/PLE	50	25	82	92	73x73	58x58	7	101	280	71.10 €
RIM63-550/PLE	63	28	103	118	90x90	70x70	9	125	550	96.62 €
RIM75-800/PLE	75	30	120	132	95x95	70x70	11	142	800	106.81 €
RIM75-1000/PLE	75	30	120	132	95x95	70x70	11	142	1000	127.36 €

Dimensions in mm

Altri prodotti...



BLHT60

Rinvio angolare a T, da 26 a 70 Nm



DKGS

Giunto senza gioco Gerwah®, da 0.5 a 3Nm



VLBG

Anello di sollevamento, Girevole



G0

Ingranaggio dritto acciaio, Acciaio 20NCD2



CCL

Capocorda ad occhiello, Acciaio



KS

Chiavetta in barre, Inox - in barre



PR105

Piede fissabile con snodo - poliammide, Ø 103



PLM-SC

Magnete piatto con foro svasato, Con foro fresato



CHAM5270SS

Cerniera ad avvitare inox, Marine



PAT123

Piede snodato con base lamiera Ø123, Ø



PRF1932

Profilato alluminio standard, 19 x 32 mm



CFS

Perno folle mini, Miniatura

Prodotti correlati



RIMtce

Ruota di livellamento, Con foro centrale



PDR-RD

Piede con ruota integrata, Ruota disassata