

Polyamide wheel

For loads up to 600kg

RPC

- Light coloured Polyamide wheel
- Smooth central bore
- Working temperature range: -30°C to +80°C

Advantages

- Shock and abrasion resistant
- Does not stain floors
- Does not mark floors
- Resists most chemical agents
- Low rolling resistance
- For solid and hard floors
- Ideal for use in wet and dirty environments (fish markets, butcher shops, canneries)



For smooth surfaces



ØD



B



C



ØA

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	C	ØA	Maximum load (kg)	Stock*	Price each 1 to 9
RPC60-31/ML	60	31	40	12	200	✓	2,06 €
RPC80-32/ML	80	32	40	12	250	✓	2,14 €
RPC100-32/ML	100	32	40	12	300	✓	2,83 €
RPC100-35/ML	100	35	48	15	350	-	9,76 €
RPC125-36/ML	125	36	50	15	350	-	5,16 €
RPC125-41/ML	125	41	59	20	400	-	10,93 €
RPC150-37/ML	150	37	49	15	400	-	8,19 €
RPC160-40/ML	160	40	58	20	500	-	22,48 €
RPC200-50/ML	200	50	58	20	600	-	24,41 €

Dimensions in mm

0 825 88 6000
Service 0,15 € / min
+ prix appel

Fax

cial2@hpceurope.com

HPC

SUPPLEMENT 2019

265

Altri prodotti...



RPCplss
Ruota girevole a doppio bloccaggio, Inox - poliammide



RFK38B
Riduttore ipoide inox, fino a 200 Nm



DOMI80
Accessori di collegamento, Leva di serraggio



PSG125
Ingranaggio dritto di precisione, Acciaio 35NCD6 pretrattato



H1
Ingranaggio elicoidale ad assi incrociati a 90°, Acciaio 20NCD2



P45
Riduttore a ruota e vite senza fine, fino a 40 Nm



RFK28B
Riduttore ipoide inox, fino a 130 Nm



CHMX_CHMDX
Albero per riduttore a ruota e vite senza fine CHMR e CHM, Albero se...



MBEX
Riduttore manuale, Manovella estremità



MRAeco
Maglia rapida economica, Acciaio



H02
Giunto cardanico semplice ad aghi,



DB
Ingranaggio conico in acciaio, 2:1

Prodotti correlati



RPCpl
Ruota fissa con piastra, Acciaio - Poliammide



RPCpl
Ruota girevole con piastra, Acciaio - Poliammide



RPCpl
Ruota girevole a doppio bloccaggio, Acciaio - poliammide



RPCplss
Ruota girevole con piastra, Inox - Poliammide