
RPP type belt by the metre

Pitch
RPP5
RPP8
RPP14

Polyurethane with steel core




For linear positioning


- ***For linear movements***
- *5mm, 8mm and 14mm pitches*
- *Fixed using rigid connecting plate*


Applications
- *Reciprocating movements*


Accessories
- **RPP.../P** *connecting plates*
- **HTD** *pulleys*

Info.
- *Minimum length 1000mm*
- *Supplied in multiples of 1 metre*
- *When ordering, add the length (L) and width (l)to the part number* **(RPP5M/L/l)**
  E.g. : **RPP5M/1000/15**









Typical application

DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-7%	On request

Part number	Pitch	Price each 1 to 5 per metre for widths of 15mm	20mm	25mm	30mm	50mm	55mm	85mm
RPP5M	RPP5	14,06 €	-	25,78 €	-	-	-	-
RPP8M	RPP8		22,51 €	-	29,90 €	35,70 €	-	-
RPP14M	RPP14	-	-	-	-	-	62,80 €	103,83 €

Dimensions in mm

Altri prodotti...



Fissaggio, Fissaggio standard



Volantino pieno, Poliammide



Perno folle mini, Miniatura



Cerniera ad avvitare, Sfilabile



Pressore a molla con intaglio e puntale a sfera, Corpo plastica + sf...



Piede fissabile con base lamiera Ø100, Ø 100




Mini martinetto motorizzato 4A, 4 ampere



Chiusura a farfalla, Tolleranze di montaggio normali



Anello di sollevamento, Orientabile femmina



Ruota per vite senza fine , Bronzo



Perno autobloccante inox temprato ad anello, Con impugnatura ad



Elemento di trascinamento, Elemento di trascinamento

Prodotti correlati



Piastra di giunzione per cinghia RPP, RPP14