Free running wheel


Stock

RUR

For loads up to 275kg

- **Light industrial wheel for loads up to 275kg**
- Ball bearing hub
- Materials:
  Polyurethane covered wheel 85 Shore
  Aluminium core
- Working temperature range: -30 to +80°C

For rough floors




Advantages

- Smooth and quiet running
- Resists wear
- Very strong
- Recommended for its exceptional resistance and its long-term service
- Low risk of flat spots developing if the wheel is not used

Applications

- Rough floors
- Can be used where metal chips, solvents, oil or grease is present



DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	A	F	Max load (kg)	Stock*	Price each 1 to 9
RUR80	80	40	41	12	175	✔	20,58 €
RUR100	100	40	41	12	220	-	23,30 €
RUR125	125	38	50	15	250	-	26,62 €
RUR150	150	40	50	20	275	-	37,75 €

*Depending on availability -Dimensions in mm

Free running wheel with mounting plate

For loads up to 275kg

RURP

- ***Light industrial castor for loads up to 275kg***
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- ***Hub with ball bearing***
- Materials:
  Top bracket/plate: Plated steel sheet
  Polyurethane covered wheel 85 Shore
  Aluminium core, (see **RUR tome 5 p.62**)
- Working temperature range: -30 to +80°C



Fixed



Swivel

Advantages

- Smooth and quiet running
- Resists wear
- Very strong
- Recommended for its exceptional resistance and its long-term service
- Low risk of flat spots developing if the wheel is not used

For rough floors



Swivel with double brake

Applications

- Rough floors
- Can be used where metal chips, solvents, oil or grease is present



ØD



B



H



L



M



ØT



ØK

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	H	L	M	ØT	Swivel inter-ference ØK	Max load (kg)	Price each 1 to 9
Fixed									
RURP80/F	80	40	110	110x85	80x60	8	-	175	31,10 €
RURP100/F	100	40	127	110x85	80x60	8	-	220	34,16 €
RURP125/F	125	38	155	110x85	80x60	8	-	250	38,38 €
RURP150/F	150	40	181	110x85	80x60	8	-	275	49,59 €
Swivel									
RURP80/P	80	40	110	110x85	80x60	8	162	175	35,76 €
RURP100/P	100	40	127	110x85	80x60	8	184	220	39,07 €
RURP125/P	125	38	155	110x85	80x60	8	216	250	43,74 €
RURP150/P	150	40	181	110x85	80x60	8	244	275	54,75 €
Swivel with double brake									
RURP80/PDB	80	40	110	110x85	80x60	8	290	175	27,46 €
RURP100/PDB	100	40	127	110x85	80x60	8	290	220	30,33 €
RURP125/PDB	125	38	155	110x85	80x60	8	290	250	35,01 €
RURP150/PDB	150	40	181	110x85	80x60	8	290	275	48,92 €

Dimensions in mm

Free running wheel with central hole

RURT — For loads up to 275kg

- **Light industrial castor for loads up to 275kg**
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- **Hub with ball bearing**
- Materials:
  Top bracket/plate: Plated steel sheet
  Polyurethane covered wheel, 85 Shore
  Aluminium core (see **RUR tome 5 p.62**)
- Working temperature range: -30 to +80°C



Swivel

For rough floors



Swivel with double brake

Advantages

- Smooth and quiet running
- Resists wear
- Very strong
- Recommended for its exceptional resistance and its long-term service
- Low risk of flat spots developing if the wheel is not used

Applications

- Rough floors
- Can be used where metal chips, solvents, oil or grease is present



DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	H	ØE	Swivel interference ØK	Max load (kg)	Price each 1 to 9
Swivel							
RURT80/P	80	40	106	12	162	175	30,18 €
RURT100/P	100	40	126	12	184	220	32,89 €
RURT125/P	125	38	153	12	216	250	37,38 €
RURT150/P	150	40	180	12	244	275	37,38 €
Swivel with double brake							
RURT80/PDB	80	40	106	12	290	175	36,10 €
RURT100/PDB	100	40	126	12	290	220	39,15 €
RURT125/PDB	125	38	153	12	290	250	43,58 €
RURT150/PDB	150	40	180	12	290	275	58,08 €

Dimensions in mm

Altri prodotti...



Piede senza snodo, Piede snodato oscillante fissabile Ø110



Square decorative screwed hinges, carbon fibre reinforced



Sfera portante fissaggio con perno filettato, Forte



Supporto per vite trapezoidale, Supporto Drylin® fisso




Pattino Drylin® W, Pattino



Maglia rapida, Inox



Braccio di reazione, Braccio di reazione per riduttori CHM e CHMR



Riduttore a rinvio angolare, da 3 a 41 Nm




Spazzola antistatica, Standard



Ingranaggio conico in plastica stampata, 1:1



Pressore a molla con intaglio e puntale a sfera, LONG-LOK -



Mini tavola di posizionamento a vite metrica, Piastra

Prodotti correlati



Ruota fissa con piastra, Poliuretano - Mozzo alluminio (Ultra scorre...



Rotella girevole con piastra, Poliuretano - Mozzo alluminio (Ultra s...



Ruota girevole a doppio bloccaggio, Poliuretano - Mozzo alluminio (U...



Ruota girevole a foro centrale, Poliuretano - Mozzo alluminio (Ultra...