

Free running wheel with mounting plate

For loads up to 350kg

RURP

- Light industrial castor for loads up to 350kg
- Materials:
 - Top bracket/plate: Plated steel sheet
 - Polyurethane covered wheel 85 Shore
 - Aluminium rim
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Hub with ball bearing
- Working temperature range: -30 to +80°C

Swivel with double lock




Advantages

- Smooth and quiet running
- Resists wear
- Very strong
- Recommended for its exceptional resistance and its long-term service
- Low risk of flat spots developing if the wheel is not used

For rough floors

Applications

- Rough floors
- Can be used where metal chips, solvents, oil or grease is present



DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Références	ØD	H	B	A	F	L	M	ØT	Swivel inter-farence ØK	Max load (kg)	Price each 1 to 9
Swivel											
RURP80/P	80	110	40	12	41	110x85	80x60	8	162	180	26,87 €
RURP100/P	100	127	40	12	41	110x85	80x60	8	184	220	29,51 €
RURP125/P	125	155	40	15	41	110x85	80x60	8	216	260	33,17 €
RURP150/P	150	181	40	20	50	110x85	80x60	8	244	350	42,85 €
Swivel with double brake											
RURP80/PDB	80	110	40	12	41	110x85	80x60	8	290	180	30,91 €
RURP100/PDB	100	127	40	12	41	110x85	80x60	8	290	220	33,76 €
RURP125/PDB	125	155	40	15	41	110x85	80x60	8	290	260	37,79 €
RURP150/PDB	150	181	40	20	50	110x85	80x60	8	290	350	47,31 €
Fixed											
RURP80/F	80	110	40	12	41	110x85	80x60	8	-	180	23,73 €
RURP100/F	100	127	40	12	41	110x85	80x60	8	-	220	26,21 €
RURP125/F	125	155	40	15	41	110x85	80x60	8	-	260	30,25 €
RURP150/F	150	181	40	20	50	110x85	80x60	8	-	350	40,35 €

Dimensions in mm

0 825 88 6000

Service 0,15 € / min
+ prix appel

Fax

cial2@hpceurope.com

HPC

SUPPLEMENT 2019

277

Altri prodotti...



GLT3E-50

Guide telescopiche
acciaio, Estensione
extra



PSG05S

Ingranaggio dritto di
precisione, Inox 316



SH2

Ingranaggio elicoidale
ad assi paralleli,
Acciaio 20NCD2



BOX-SHNA

Dado esagonale -
DIN934, Valigetta di
dadi acciaio



AT5-10ECO

Puleggia dentata di
posizionamento tipo
AT, Serie economica -
AT5 al...



UGPC

Unità di guida per
cilindrico, Cuscinetto
corto



PRS80

Piede snodato tutto
inox Ø80, Ø 80



DOMI30

Kit di raccordo, Kit di
raccordo XY



CHB

Single output shaft,
For CHB gearbox



AC156-157

Riscontro per chiusura
a leva rigida ad



PSG15S

Ingranaggio dritto di
precisione, Inox 316



CHA1056_U20

Cerniera ad avvitare,
Sezione 90X60

Prodotti correlati



RPCpl

Ruota fissa con
piastra, Acciaio -
Poliammide



RUR

Ruota, Poliuretano -
Mozzo alluminio (Ultra
scorrevole)



RBNpl

Ruota fissa con
piastra, Acciaio -
caucciù



RBGpl

Ruota fissa con
piastra, Acciaio -
gomma grigia