

Free running wheel

Stock

RUR

For loads up to 275kg

- Light industrial wheel for loads up to 275kg
- Ball bearing hub
- Materials:
 - Polyurethane covered wheel 85 Shore
 - Aluminium core
- Working temperature range: -30 to +80°C

For rough floors



Advantages

- Smooth and quiet running
- Resists wear
- Very strong
- Recommended for its exceptional resistance and its long-term service
- Low risk of flat spots developing if the wheel is not used

Applications

- Rough floors
- Can be used where metal chips, solvents, oil or grease is present



ØD



B



C



ØA

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	A	F	Max load (kg)	Stock*	Price each 1 to 9
RUR80	80	40	41	12	175	✓	20,58 €
RUR100	100	40	41	12	220	-	23,30 €
RUR125	125	38	50	15	250	-	26,62 €
RUR150	150	40	50	20	275	-	37,75 €

*Depending on availability -Dimensions in mm

Free running wheel with mounting plate

For loads up to 275kg

RURP

- Light industrial castor for loads up to 275kg
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Hub with ball bearing
- Materials:
 - Top bracket/plate: Plated steel sheet
 - Polyurethane covered wheel 85 Shore
 - Aluminium core, (see RUR tome 5 p.62)
- Working temperature range: -30 to +80°C



Fixed



Swivel

Advantages

- Smooth and quiet running
- Resists wear
- Very strong
- Recommended for its exceptional resistance and its long-term service
- Low risk of flat spots developing if the wheel is not used

For rough floors



Swivel with double brake

Applications

- Rough floors
- Can be used where metal chips, solvents, oil or grease is present



ØD



B



H



L



M



ØT



ØK

DISCOUNTS

Qty	1+	10+	30+
Disc. List	-5%	-5%	On request

Part number	ØD	B	H	L	M	ØT	Swivel interference ØK	Max load (kg)	Price each 1 to 9
Fixed									
RURP80/F	80	40	110	110x85	80x60	8	-	175	31,10 €
RURP100/F	100	40	127	110x85	80x60	8	-	220	34,16 €
RURP125/F	125	38	155	110x85	80x60	8	-	250	38,38 €
RURP150/F	150	40	181	110x85	80x60	8	-	275	49,59 €
Swivel									
RURP80/P	80	40	110	110x85	80x60	8	162	175	35,76 €
RURP100/P	100	40	127	110x85	80x60	8	184	220	39,07 €
RURP125/P	125	38	155	110x85	80x60	8	216	250	43,74 €
RURP150/P	150	40	181	110x85	80x60	8	244	275	54,75 €
Swivel with double brake									
RURP80/PDB	80	40	110	110x85	80x60	8	290	175	27,46 €
RURP100/PDB	100	40	127	110x85	80x60	8	290	220	30,33 €
RURP125/PDB	125	38	155	110x85	80x60	8	290	250	35,01 €
RURP150/PDB	150	40	181	110x85	80x60	8	290	275	48,92 €

Dimensions in mm

Free running wheel with central hole

RURT

For loads up to 275kg

- Light industrial castor for loads up to 275kg
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Hub with ball bearing
- Materials:
 - Top bracket/plate: Plated steel sheet
 - Polyurethane covered wheel, 85 Shore
 - Aluminium core (see RUR tome 5 p.62)
- Working temperature range: -30 to +80°C



Swivel

For rough floors



Swivel with double brake

Advantages

- Smooth and quiet running
- Resists wear
- Very strong
- Recommended for its exceptional resistance and its long-term service
- Low risk of flat spots developing if the wheel is not used

Applications

- Rough floors
- Can be used where metal chips, solvents, oil or grease is present



ØD



B



H



ØE



ØK

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	H	ØE	Swivel interference ØK	Max load (kg)	Price each 1 to 9
Swivel							
RURT80/P	80	40	106	12	162	175	30,18 €
RURT100/P	100	40	126	12	184	220	32,89 €
RURT125/P	125	38	153	12	216	250	37,38 €
RURT150/P	150	40	180	12	244	275	37,38 €
Swivel with double brake							
RURT80/PDB	80	40	106	12	290	175	36,10 €
RURT100/PDB	100	40	126	12	290	220	39,15 €
RURT125/PDB	125	38	153	12	290	250	43,58 €
RURT150/PDB	150	40	180	12	290	275	58,08 €

Dimensions in mm

Altri prodotti...




GBSz

Vite a ricircolo di sfere, Dado cilindrico



DTR

Pignone tendicateni, Ruota dentata in acciaio



PM4

Ruota per vite senza fine, Plastica lavorata (delrin)



ARTE

Silent block, Carico multidirezionale



GEC

Chiusura a leva in gomma con aggancio, Bloccabile



GP75

Chiusura a leva molla a trazione compensata, Standard (GP75)



CRLHR

Anello di sollevamento,



MHQMEP

Manovella ad impugnatura girevole, Alesaggio quadrato



HW_HT

Guida su semi-binari, Ruota



SLB

Pistoncino a molla, inox



AT5M AT10M

Cinghia aperta al metro tipo AT, AT10 Poliuretano armatura



LC

Limitatore di coppia ad attrito, 190 a 1800 Nm

Prodotti correlati



RUR

Ruota, Poliuretano - Mozzo alluminio (Ultra scorrevole)



RPCpl

Ruota girevole con piastra, Acciaio - Poliammide



RBNpl

Ruota girevole con piastra, Acciaio - caucciù



RURp

Ruota fissa con piastra, Poliuretano - Mozzo alluminio (Ultra scorrevole)