
Manual worm/wheel gearbox

RVM14

Manual torque up to 5 Nm

- ***Manually operated gearbox***
- *Ratios from 1:1 to 23:1*
- *Materials:*
  Housing: Die cast zinc
  Worm/wheel: Case hardened steel

NUOVO !




Info


- *Not suitable for motorised applications*

Accessories

- ***MBEX** handle* **(tome 2 p.125)**
- ***AHEX** hexagonal shaft* **(tome 2 p.124)**



For manual operation only



DISCOUNTS

Qty	1+	10+	25+	50+
Disc.	List	-5%	-15%	On request

Part number	Ratio	Input/ Output	Max torque (Nm)	Self locking	Stock*	Price each 1 to 9
RVM14-1	1:1	hex 6mm	2,0	No	✔	130,78 €
RVM14-2	2:1	hex 6mm	2,0	No	✔	130,78 €
RVM14-2.8	2,8:1	hex 6mm	2,5	No	-	117,17 €
RVM14-4.33	4,33:1	hex 6mm	2,0	Yes	✔	117,17 €
RVM14-10	10:1	hex 6mm	4,0	Yes	✔	130,78 €
RVM14-14	14:1	hex 6mm	5,0	Yes	✔	130,78 €
RVM14-15	15:1	hex 6mm	4,0	Yes	✔	127,19 €
RVM14-23	23:1	hex 6mm	3,0	Yes	-	117,17 €

**Depending on availability - Dimensions in mm*

Manually operated gearbox

Manual torque up to 17 Nm

RVM25

- ***Compact manually operated gearbox***
- *Ratios from 1:1 to 30:1*
- *Material:*
  Housing: Die cast zinc

Info


- *Not suitable for motorised applications*


Accessories

- **MBEX** *handle* **(tome 2 p.125)**
- **AHEX** *hexagonal shaft* **(tome 2 p.124)**



NUOVO !





For manual operation only

DISCOUNTS

Qty	1+	10+	25+	50+
Disc.	List	-5%	-15%	On request

Part number	Ratio	Input	Output	Max torque (Nm)	Self locking	Stock*	Price each 1 to 9
RVM25-1	1:1	hex 6mm	hex 9mm	2,0	No	✔	163,72 €
RVM25-2	2:1	hex 6mm	hex 9mm	3,0	No	✔	177,68 €
RVM25-3.25	3,25:1	hex 6mm	hex 9mm	4,0	Yes	✔	163,47 €
RVM25-4.33	4,33:1	hex 6mm	hex 9mm	5,0	Yes	✔	163,47 €
RVM25-7	7:1	hex 6mm	hex 9mm	7,0	Yes	✔	165,47 €
RVM25-8.5	8,5:1	hex 6mm	hex 9mm	9,0	Yes	✔	175,73 €
RVM25-17	17:1	hex 6mm	hex 9mm	12,0	Yes	✔	203,42 €
RVM25-20	20:1	hex 6mm	hex 9mm	15,0	Yes	✔	166,59 €
RVM25-30	30:1	hex 6mm	hex 9mm	17,0	Yes	✔	169,42 €

**Depending on availability - Dimensions in mm*

Hexagonal shaft DIN176


AHEX For manually operated manual gearbox


- ***Hexagonal shaft for use with the RAM and RVM manual gearbox ranges***
- *Cut to required length*
- *Material:*
  Steel

Accessories

- **RAM** *operated gearbox* ***(tome 2 p.120)***
- **RVM** *operated gearbox* ***(tome 2 p.122)***







Typical application

DISCOUNTS

Qty	1+	10+	25+	50+
Disc.	List	-5%	-15%	On request

Part number	Profil	Length (mm)	Stock*	Price each 1 to 9
AHEX6-1000	hex 6mm	1000	✔	35,05 €
AHEX7-1000	hex 7mm	1000	✔	38,18 €
AHEX9-1000	hex 9mm	1000	✔	38,18 €

**Depending on availability - Dimensions in mm*

Hexagonal ended handle

For use with manually operated gearbox

MBEX


- ***Handle for operating RAM and RVM manual gearboxes***
- *Material:*
  Shaft: stainless steel
  Rotating handle: plastic




NUOVO !

Accessories

- **RAM** operated gearbox **(tome 2 p.120)**
- **RVM** operated gearbox **(tome 2 p.122)**





DISCOUNTS

Qty	1+	10+	25+	50+
Disc.	List	-5%	-15%	On request

Part number	A	H	ØD	E	B	Stock*	Price each 1 to 9
MBEX6-90	90	hex 6mm	7	60	20	✔	88,21 €
MBEX7-90	90	hex 7mm	8	62	15	✔	80,17 €

**Depending on availability - Dimensions in mm*